


Data Sheet



No.	84001500
Connector Type:	CMP MC 32 PINK
DRAKA Cable Types:	COAX15 AD 06 S

Band Width:	5 MHz – 2,2 GHz
Impedance:	75 Ohm
Amp. Rating:	2 A
Shielding:	>108 db @ 900 MHz

Temperature	
Installing:	-5 to +50 °C
Operating:	-30 to +60 °C
Sealing Test:	IP X8

Return Loss: @ MHz, Better Than	
500:	-39 dB
860:	-39 dB
1000:	-39 dB
1750:	-34 dB

Insertion Loss: @ MHz, Better Than	
500:	0,1 db
860:	0,1 db
1000:	0,1 db
1750:	0,16 db

Pull Strength:	
Cable:	3,3 kg

Dielectric Strength:	2 kV
Insulation Resistance:	(@500V): > 29,99 Gohm
Inner Conductor:	Resistance 1 mΩ / 1A DC.

Material and Plating		
Body	Brass	Ni
Compression ring	Delrin 527	