

Hardware for Electrical Work

UL LISTED, CSA CERTIFIED AS NOTED

Nylon-insulated butt splices



Part Number	Size AWG	Color	Standard Package
21-001	22 - 18	Red	100
21-002	16 - 14	Blue	100
21-009	12 - 10	Yellow	100



ScotchLok® components



Part Number	Size AWG	Type	Standard Package
22-000	18 - 14	Style 560 - blue	100
22-001	22 - 16	Style 557 pigtail - red	100
22-020	22 - 16	Style 558 tap - red	100
22-021	12 - 10	Style 562 tap - yellow	100



Wire nuts



Part Number	Size AWG	Type	Standard Package
22-004	18 - 10	76B - red	100
22-005	18 - 12	74B - yellow	100
22-003	22 - 14	73B - orange	100
22-010	22 - 14	72B - blue	100
22-009	22 - 16	71B - gray	100



Wire joints



Part Number	Description	Standard Package
22-031	Wire joint, min. 2 #24, max. 3 #18	100
22-032	Wire joint, min. 4 #18, max. 2 #12	100



Cable ties and mounting base



Part Number	Length Inches	Max. Width Inches	Standard Package
23-001	4.0	.095	100
23-004	6.1	.141	100
23-002	8.0	.185	100
23-012	11.1	.141	100
23-003	14.9	.275	100
23-013	30.7	.275	100
23-032	Mounting Base	.19	100

Mounting base is UR rated and not UL listed.



Wire marker cards and dispensers

Part Number	Description	Standard Package
25-001	Wire marker cards, nos. 1 - 33	25
25-003	Wire marker cards, nos. 34 - 66	25
25-005	Wire marker cards, nos. 67 - 99	25
25-006	Wire marker dispenser	1



Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.

Hardware for Electrical Work

UL LISTED, CSA CERTIFIED

Mechanical lugs



Part Number	Wire Size / Hole Size AWG	Standard Package
17-002	14-6 / #10	100
17-005	1/0-4/0 / 3/8 in.	10
17-001	8-2 / 1/4 in.	50
17-031	14-6 / 3/8 in.	10
17-032	4-2/0 / 3/8 in.	10



Ring terminals



Part Number	Wire Size / Type AWG	Standard Package
20-015	22-18 insulated - red #6 ring	100
20-026	22-18 non-insulated #8 ring	100
20-002	22-18 insulated - red #10 ring	100
20-001	18-14 non-insulated #10 ring	100
20-003	16-14 insulated - blue #10 ring	100
20-113	16-14 insulated - blue #8 ring	100



Compression lugs



Part Number	Wire Size / Hole Size AWG	Standard Package
17-019	1/0 / 3/8 in.	10
17-034	2/0 / 3/8 in.	10
17-035	3/0 / 3/8 in.	10
17-036	4/0 / 3/8 in.	10
17-015	1 / 3/8 in.	20
17-020	2 / 3/8 in.	25
17-021	4 / 3/8 in.	50
17-037	6 / 3/8 in.	50
17-022	8 / 3/8 in.	50
17-008	1 / 1/2 in.	20



Fork terminals



Part Number	Wire Size / Type AWG	Standard Package
20-012	22-18 non-insulated #6 fork	100
20-048	22-18 insulated - red #6 fork	100
20-019	22-18 insulated - red #8 fork	100
20-020	22-18 insulated - red #10 fork	100
20-016	16-14 insulated - blue #6 fork	100
20-017	16-14 insulated - blue #8 fork	100
20-018	16-14 insulated - blue #10 fork	100



Female disconnects



Part Number	Type and Size	Standard Package
20-004	#22-18 non-insulated .110 x .032 in.	100
20-047	#22-18 insulated .110 x .032 in.	100



Tape



Part Number	Description All Tape 3/4" Wide	Standard Package
16-006	#33 black electrical, 66 ft.	10
16-008	#35 white electrical, 66 ft.	10
16-009	#35 red electrical, 66 ft.	10
16-010	#35 blue electrical, 66 ft.	10
16-011	#35 green electrical, 66 ft.	10
16-012	#35 yellow electrical, 66 ft.	10
16-013	#35 orange electrical, 66 ft.	10
16-014	#35 brown electrical, 66 ft.	10
16-002	Friction, 60 ft.	1
16-003	Rubber, 22 ft.	1
16-005	#1700 electrical, 60 ft.	10



Split bolt connectors



Part Number	Wire Size / Type AWG	Standard Package
17-041	1-3/0	25
17-046	2-6	100
17-073	4-8	100
17-086	10-12	100



Lights and electrical

Part Number	Description
36-070	Rough service bulbs, 100 watt, package of 60
37-001	Porcelain fixture, with collar and pull chain
37-021	Plastic cage
36-033	Drop light with cage and hook, 25 ft. cord
36-034	Drop light with cage and hook, 50 ft. cord
37-178	GFCI with cover, 125VAC, 15A

Use these tools for crimping. See page 92 for details.

Draka QuickCrimp



Crimping tool



Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.