

EMT Conduit Bodies and EMT-to-Flex Couplings

UL LISTED, CSA CERTIFIED

Type LB / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-011	1/2	10
30-012	3/4	10
30-013	1	5
30-014	1-1/4	2
30-015	1-1/2	2
30-021	2	1
30-023*	2-1/2	1

*30-023 comes with cover



Type LR / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-030	1/2	10
30-031	3/4	10
30-032	1	5
30-033	1-1/4	2
30-034	1-1/2	2
30-035	2	1



Type LL / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-040	1/2	10
30-041	3/4	10
30-042	1	5
30-043	1-1/4	2
30-044	1-1/2	2
30-045	2	1



Covers for conduit bodies

Part Number	Trade Sizes	Standard Package
30-017	1/2	50
30-018	3/4	50
30-019	1	50
30-020	1-1/4 to 1-1/2	50
30-022	2	25



EMT-to-flex compression couplings - malleable iron



Part Number	Trade Sizes	Standard Package
69-049	1/2 EMT to 3/8 flex	25
69-048	1/2 EMT to 1/2 flex	20
69-050	3/4 EMT to 3/4 flex	10
12-004	1 EMT to 1 flex	10
12-006	1-1/4 EMT to 1-1/4 flex	5
12-007	1-1/2 EMT to 1-1/2 flex	5
12-005	2 EMT to 2 flex	2



EMT-to-flex squeeze couplings - set screw/die-cast



Part Number	Trade Sizes	Standard Package
12-001	1/2 EMT to 3/8 flex	50
12-002	1/2 EMT to 1/2 flex	25
12-003	3/4 EMT to 3/4 flex	25
12-016	1 EMT to 1 flex	25



EMT-to-flex couplings

Part Number	Trade Sizes	Standard Package
12-012	1/2 EMT to flex	50
12-013	3/4 EMT to flex	25



Wireway and
Electrical

Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.

Flexible Conduit and Fittings

UL LISTED, CSA CERTIFIED AS NOTED

Thin-wall steel conduit

Part Number	Trade Sizes	Standard Package
03-001	3/8	2000 ft. reel
03-002	1/2	1000 ft. reel
03-003	3/4	500 ft. reel
03-004	1	50 ft. coil
03-005	1-1/4	50 ft. coil
03-006	1-1/2	50 ft. coil
03-007	2	25 ft. coil



Malleable iron 90° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
69-028	3/8	50
69-029	1/2	25
69-030	3/4	10
69-031	1	5
69-032	1-1/4	25
69-033	1-1/2	5



Die-cast 90° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
11-001	3/8	50
11-002	1/2	25
11-003	3/4	10
11-004	1	5
11-005	1-1/4	10
11-006	1-1/2	5
11-008	2	5



Malleable iron straight squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
69-035	3/8	50
69-036	1/2	50
69-037	3/4	25
69-038	1	25
69-039	1-1/4	25
69-040	1-1/2	5
69-041	2	10



Die-cast straight squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
10-001	3/8	50
10-002	1/2	25
10-003	3/4	25
10-004	1	10
10-005	1-1/4	10
10-006	1-1/2	5
10-010	2	10



Screw-in connectors for flex

Part Number	Trade Sizes	Standard Package
10-021	1/2	50
10-022	3/4	25
10-023	1	25
10-035	1-1/4	10
10-029	1-1/2	10
10-036	2	10
11-045	90° 'Jake L' for 1/2	25
11-046	90° 'Jake L' for 3/4	15
11-064	90° 'Jake L' for 1	10



Die-cast 45° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
11-034	3/8	25
11-035	1/2	10
11-036	3/4	50



Screw-in couplings for flex

Part Number	Trade Sizes	Standard Package
12-101	1/2	50
12-102	3/4	25
12-100	1	15



Roto-Flex cutter for flexible conduit - see page 92 for details.



Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.