

# EMT Conduit Bodies and EMT-to-Flex Couplings

UL LISTED, CSA CERTIFIED

## Type LB / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-011	1/2	10
30-012	3/4	10
30-013	1	5
30-014	1-1/4	2
30-015	1-1/2	2
30-021	2	1
30-023*	2-1/2	1

\*30-023 comes with cover



## Type LR / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-030	1/2	10
30-031	3/4	10
30-032	1	5
30-033	1-1/4	2
30-034	1-1/2	2
30-035	2	1



## Type LL / set screw (cover separate)



Part Number	Trade Sizes	Standard Package
30-040	1/2	10
30-041	3/4	10
30-042	1	5
30-043	1-1/4	2
30-044	1-1/2	2
30-045	2	1



## Covers for conduit bodies

Part Number	Trade Sizes	Standard Package
30-017	1/2	50
30-018	3/4	50
30-019	1	50
30-020	1-1/4 to 1-1/2	50
30-022	2	25



## EMT-to-flex compression couplings - malleable iron



Part Number	Trade Sizes	Standard Package
69-049	1/2 EMT to 3/8 flex	25
69-048	1/2 EMT to 1/2 flex	20
69-050	3/4 EMT to 3/4 flex	10
12-004	1 EMT to 1 flex	10
12-006	1-1/4 EMT to 1-1/4 flex	5
12-007	1-1/2 EMT to 1-1/2 flex	5
12-005	2 EMT to 2 flex	2



## EMT-to-flex squeeze couplings - set screw/die-cast



Part Number	Trade Sizes	Standard Package
12-001	1/2 EMT to 3/8 flex	50
12-002	1/2 EMT to 1/2 flex	25
12-003	3/4 EMT to 3/4 flex	25
12-016	1 EMT to 1 flex	25



## EMT-to-flex couplings

Part Number	Trade Sizes	Standard Package
12-012	1/2 EMT to flex	50
12-013	3/4 EMT to flex	25



Wireway and  
Electrical

Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.

# Flexible Conduit and Fittings

UL LISTED, CSA CERTIFIED AS NOTED

## Thin-wall steel conduit

Part Number	Trade Sizes	Standard Package
03-001	3/8	2000 ft. reel
03-002	1/2	1000 ft. reel
03-003	3/4	500 ft. reel
03-004	1	50 ft. coil
03-005	1-1/4	50 ft. coil
03-006	1-1/2	50 ft. coil
03-007	2	25 ft. coil



## Malleable iron 90° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
69-028	3/8	50
69-029	1/2	25
69-030	3/4	10
69-031	1	5
69-032	1-1/4	25
69-033	1-1/2	5



## Die-cast 90° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
11-001	3/8	50
11-002	1/2	25
11-003	3/4	10
11-004	1	5
11-005	1-1/4	10
11-006	1-1/2	5
11-008	2	5



## Malleable iron straight squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
69-035	3/8	50
69-036	1/2	50
69-037	3/4	25
69-038	1	25
69-039	1-1/4	25
69-040	1-1/2	5
69-041	2	10



## Die-cast straight squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
10-001	3/8	50
10-002	1/2	25
10-003	3/4	25
10-004	1	10
10-005	1-1/4	10
10-006	1-1/2	5
10-010	2	10



## Screw-in connectors for flex

Part Number	Trade Sizes	Standard Package
10-021	1/2	50
10-022	3/4	25
10-023	1	25
10-035	1-1/4	10
10-029	1-1/2	10
10-036	2	10
11-045	90° 'Jake L' for 1/2	25
11-046	90° 'Jake L' for 3/4	15
11-064	90° 'Jake L' for 1	10



## Die-cast 45° squeeze-type flex box connectors

Part Number	Trade Sizes	Standard Package
11-034	3/8	25
11-035	1/2	10
11-036	3/4	50



## Screw-in couplings for flex

Part Number	Trade Sizes	Standard Package
12-101	1/2	50
12-102	3/4	25
12-100	1	15



Roto-Flex cutter for flexible conduit - see page 92 for details.



Standard packaging quantities are listed. Parts may be ordered in less than standard quantities.