

BendBright™ OM2+ Multimode Fibre



Issue date: October 2020
Supersedes: March 2013

Applicable Standards

- IEC / EN 60793-2-10: type A1-OM2
- ISO / IEC 11801: Category OM2
- TIA / EIA 492 AAAB (formerly 492 AAAB)

Optical Specifications

Bandwidth (OFL)

Attribute	Units	Specified Values
Overfilled Modal Bandwidth at 850 nm	MHz•km	≥ 750
Overfilled Modal Bandwidth at 1300 nm	MHz•km	≥ 500

Bandwidth (EMB)

Attribute	Units	Specified Values
Effective Modal Bandwidth at 850 nm	MHz•km	≥ 950

Attenuation

Attribute	Units	Specified Values
Attenuation coefficient at 850 nm	dB/km	≤ 2.4
Attenuation coefficient at 1300 nm	dB/km	≤ 0.6

Numerical Aperture

Numerical aperture	0.200 ± 0.015	
--------------------	---------------	--

Macrobending Loss

Conditions	Wavelength	Units	Specified Values
Mandrel Radius = 7.5 mm, 2 Turns	850 / 1300 nm	dB	≤ 0.2 / ≤ 0.5
Mandrel Radius = 15 mm, 2 Turns	850 / 1300 nm	dB	≤ 0.1 / ≤ 0.3
Mandrel Radius = 37.5 mm, 100 Turns	850 / 1300 nm	dB	≤ 0.5 / ≤ 0.5

Multimode System Reach

IEEE Standard	Units	Transmission Distance
1000BASE-SX	m	750
10GBASE-SR	m	150

Chromatic Dispersion

Attribute	Conditions	Units	Specified Values
Zero Dispersion Wavelength, λ_0		nm	$1295 \leq \lambda_0 \leq 1340$
Zero Dispersion Slope, S_0	$1295 \leq \lambda_0 \leq 1310$	ps/[nm ² •km]	≤ 0.105
	$1310 \leq \lambda_0 \leq 1340$	ps/[nm ² •km]	$\leq 0.000375 (1590 - \lambda_0)$

Backscatter characteristics ¹

Attribute	Conditions	Units	Specified Values
Point Discontinuity ²	850 nm, 1300 nm	dB	≤ 0.1
Irregularities over fibre length	850 nm, 1300 nm	dB	≤ 0.1
Reflections	-	-	Not allowed
Group Index of Refraction at 850 nm	-	-	1.482 (typical)
Group Index of Refraction at 1300 nm	-	-	1.477 (typical)

¹ OTDR measurement with 0.5 μ s pulse width.

² Mean of bi-directional measurement

Geometrical Specifications

Glass Geometry

Attribute	Units	Specified Values
Core Diameter	μ m	50 ± 2.5
Core non-Circularity	%	≤ 5
Core-Cladding Concentricity Error	μ m	≤ 1.5
Cladding Diameter	μ m	125.0 ± 1.0
Cladding non-Circularity	%	≤ 1

Coating Geometry

Attribute	Units	Specified Values
Coating Diameter	μ m	242 ± 7
Coating non-Circularity	%	≤ 5
Coating-Cladding Concentricity Error	μ m	≤ 10

Mechanical Specifications

Proof Test ³

The entire spool length is subjected to a tensile proof stress ≥ 0.7 GPa (100 kpsi) ; 1% strain equivalent

³ Higher proof test available upon request

Coating Performance

Attribute	Units	Specified Values
Average Coating Strip Force, unaged and aged ⁴	N	$1 \leq F_{\text{avg-strip}} \leq 3$
Peak Coating Strip Force, unaged and aged ⁴	N	$1.3 \leq F_{\text{peak-strip}} \leq 8.9$

⁴ Aging at 23°C, 30 days

Fibre Strength

Attribute	Units	Specified Values
Dynamic Tensile Strength (0.5 meter gauge length), unaged and aged ⁵	GPa	median > 3.8 (550 kpsi)
Dynamic Fatigue, unaged and aged ⁵	-	$n_d \geq 20$

⁵ Aging at 85°C, 85% RH, 30 days

Environmental Specifications

Environmental test	Test Conditions	Induced attenuation at 850, 1300 nm (dB/km)
Temperature Cycling	-60°C to +85°C	≤ 0.1
Temperature - Humidity Cycling	-10°C to +85°C, 4-98% RH	≤ 0.1
Water Immersion	30 days; 23°C	≤ 0.1
Dry Heat	30 days ; 85°C	≤ 0.1
Damp Heat	30 days; 85°C; 85% RH	≤ 0.1

Others

Length	Up to 17.6 km per spool
Coating	Acrylate Coating; Coloured (ink) and Clear

All measurements in accordance with ITU-T G650 recommendations