

RS3000 Rack Patch Only

Prysmian Part Numbers: See below



The RS3000 Rack Patch Only is a standard rack with 19" mounting rails, used to accommodate a range of SRS3000 shelves and sub-racks or any other 19" rack mounted products. The rack is 900mm wide by 300mm in depth and is available in 47U height (2200mm). The rack is supplied with side panels and transparent doors. Mandrels are supplied in the left hand and right hand side of the rack to manage and store incoming and outgoing patchcords. The maximum capacity of the rack is 2160 fibres (based on the 47U rack on a patch only basis).

Features and Benefits

- The rack can accommodate the range of SRS3000 shelves and sub-racks. Please note that other 19" rack mounted products and equipment can be mounted into the RS3000 rack. Refer to the other products within the OAsys range.
- SRS3000 shelves and sub-racks are available in 1U, 2U or 3U formats.
- Up to 45 single (1U) SRS3000 shelves can be accommodated in the 47U rack, providing a capacity of 2160 fibres on a patch only basis.
- The rack is supplied fully configured as a composed rack with side channels, doors, 19" mounting rails and patchcord storage mandrels.
- Patchcord storage drums are supplied in the left hand and right hand side of the rack, for patchcord storage and bend management..
- The rack is suitable for patch only shelves only as no cable management brackets can be fitted.
- Locks are available for restricted access to the rack. Order lock separately XKTSC00353.

Kit Contents

The RS3000 Rack is supplied fully assembled with side panels, transparent doors, four cable anchor brackets and eleven patchcord storage mandrels.

Additional Items Recommended

- SRS 3000 Patch Only Shelf
- SRS 3000 Patchcord Storage Shelf
- SRS 3000 Sub-Racks (2U and 3U)
- Horizontal Routing and Storage Shelf
- Connectorised Splitter Modules

Prysmian Part Numbers

- XEXSC02716 – (47U) 2200 x 900 x 300
- XKTSC00353 – Door Lock Kit (individual key)

Technical Data

- Maximum Capacity:
 - 47U: 45 SRS 3000 shelves (1U)
- Maximum Fibre Capacity:
(using SRS3000 products)
 - 47U: * 2160 (patch only with SC and LC connectors)
 - 47U: * 1080 (patch only with FC, ST and E2000 connectors)
- Required space envelope (mm):-
 - 47U: (h) 2200 x (w) 900 X (d) 300
- Material: Mild Steel
- Finish: Painted light grey (RAL 7035)

Logistics

- Packing Dimensions (mm):
 - 47U: (h)2280 x (w)965 x (d)350
- Packed Weight (Kg):
 - 47U: 155.0
- Net Weight (Kg)
 - 47U: 95.0

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2014, All Rights Reserved.
The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.