

Copper indoor cables



Jumper wire (Red-White / Blue-White)

2-0.5 mm TDT 1098 REV 01

Jumper wire



Construction

Conductor Tinned solid copper bare conductor, nom. diameter 0.5mm

Insulation PVC, Nom. insulation thickness: 0.25 mm

Pair stranding Two insulated cores twisted (Max. lay length 15 cm)

Electrical properties

Conductor resistance at 20°C ± 5 °C ≤ 95 Ω/km

Insulation resistance at 20°C ± 5 °C and 500 V ≥ 1000 MΩxkm

Mutual capacitance at 800 Hz ≤ 120 nF/km

800 Hz 2,2 dB/km **Attenuation** 17,5 dB/km

300 kHz

Technical data

SAP code	Designation	Color	Delivery, m	Drum type	Weigth, Kg/km
60007220	Jumper wire	Red White	250	Coil	5
60007219	Jumper wire	Blue White	250	Coil	5