


Hinged Metal Wireway and Fittings

ETL CERTIFIED - STOCKED ONLY IN CANADA

Galvanized hinged wireway




Part Number	Dimension A inches	Dimension B inches	Length inches
UGTR 252596CSACND	2-1/2	2-1/2	96
UGTR 4496CSACND	4	4	96
UGTR 6696CSACND	6	6	96



Couplings for hinged trough




Part Number	Dimension A inches	Dimension B inches	For use with Trough P/N
UCON 2525CSACND	2-1/2	2-1/2	UGTR 252596CSACND
UCON 44CSACND	4	4	UGTR 4496CSACND
UCON 66CSACND	6	6	UGTR 6696CSACND



Flanges for hinged trough




Part Number	Dimension A inches	Dimension B inches	For use with Trough P/N
UPCN 2525CSACND	2-1/2	2-1/2	UGTR 252596CSACND
UPCN 44CSACND	4	4	UGTR 4496CSACND
UPCN 66CSACND	6	6	UGTR 6696CSACND



End caps for hinged trough



Part Number	Dimension A inches	Dimension B inches	For use with Trough P/N
UEPT 2525CSACND	2-1/2	2-1/2	UGTR 252596CSACND
UEPT 44CSACND	4	4	UGTR 4496CSACND
UEPT 66CSACND	6	6	UGTR 6696CSACND



Special size wireway is available with short lead times.
Call Draka Elevator at 1-877-372-5237 for further information.

Material: Galvanized steel


Hinged Metal Wireway and Fittings

ETL CERTIFIED - STOCKED ONLY IN CANADA

Tee fittings for hinged trough




Part Number	Dimension A inches	Dimension B inches	For use with Trough P/N
UTEE 2525CSACND	2-1/2	2-1/2	UGTR 252596CSACND
UTEE 44CSACND	4	4	UGTR 4496CSACND
UTEE 66CSACND	6	6	UGTR 6696CSACND



90° elbows for hinged trough / Type C




Part Number	Dimension A inches	Dimension B inches	For use with Trough P/N
UL90 2525CSACND	2-1/2	2-1/2	UGTR 252596CSACND
UL90 44CSACND	4	4	UGTR 4496CSACND
UL90 66CSACND	6	6	UGTR 6696CSACND



Reducers for hinged trough



Part Number	Dimension A inches	Dimension B inches
URED 442525CSACND	4 x 4	2-1/2 x 2-1/2
URED 6644CSACND	6 x 6	4 x 4



Special size wireway is available with short lead times.
Call Draka Elevator at 1-877-372-5237 for further information.

Material: Galvanized steel