

Wire Rope Accessories

DrakaLube™ wire rope treatment / lubricant


Part Number	Description
WR-DRAKALUBE	DrakaLube wire rope treatment / lubricant, one gallon jug

DrakaLube wire rope treatment / lubricant has been specifically formulated to fight bending stresses, high groove pressures and moisture. DrakaLube has additives that protect against corrosion, wear and most importantly, it can also displace moisture in the rope core.



Rope oilers for elevator hoist ropes, escalator chains and selector tapes

Part Number	Description
MIS-100	Automatic oiler, with 9" wick
MIS-102	Automatic oiler, with 12" wick
MIS-103	Extension bracket, for rope oiler
MIS-103A	Replacement wick, for all size rope oilers
MIS-103B	Replacement wick, 1/2" x 6 1/2" x 12"



The rope oiler lubricates by electrostatic attraction and requiring only minimal wick adjustment after installation. The oiler:

- Automatically lubricates rope for increased rope and sheave life
- Has an adjustable oiling rate-wick lock and wick length
- Features a top-fill external oil level indicator

Reeving splices

Part Number	Color Code	For Rope Size inches	Length inches	Rod Diameter inches	Max. Load lbs
RS-2103	Yellow	3/8	22	.051	300
RS-2105	Orange	1/2	29	.070	2000
RS-2107	Black	5/8	36	.086	2000



Reeving splices are provided three to a package. Use only once, then discard. Use ONLY for right lay ropes. Other sizes are available.

Cable bands

Part Number	Description	Standard Packaging
WR-CB-38	Cable bands for 3/8 in. rope	50
WR-CB-12	Cable bands for 1/2 in. rope	50
WR-CB-58	Cable bands for 5/8 in. rope	50



Wire rope clips - malleable iron

Part Number	Description
79-107	1/8 in. wire rope clip
79-114	3/16 in. wire rope clip
79-122	1/4 in. wire rope clip
79-123	3/8 in. wire rope clip
79-126	1/2 in. wire rope clip
79-127	5/8 in. wire rope clip



Selector / hoistway door relating cable - preformed, flexible, zinc-coated

Part Number	Size inches	Stranding	MBL lbs	Cable Weight lbs/kft
040219	1/16	7 x 7	480	7.5
040218	3/32	7 x 7	920	16
040215	1/8	7 x 19	2,000	29
040216	5/32	7 x 19	2,800	45
040220	3/16	7 x 19	4,200	65
040225	1/4	7 x 19	7,000	110



DO NOT use selector / hoistway door relating cable for hoisting applications.

Wire Rope, Compensation and Accessories