



Industrial Specialties - Solar

Photovoltaic Cables

PRYSUN™

PRYSUN™ SOLAR PV Cables

PRYSUN™ H1Z2Z2-K, 62930 IEC 131 Halogen Free Low Smoke cables are intended for use in photovoltaic systems at nominal voltage rating of 1,5 kV DC.

APPLICATION

PRYSUN™ solar PV cables are designed for the interconnection of various elements in photovoltaic systems, including panel interconnection, between panels and string boxes or from string boxes to the inverter. They are suitable for applications in/at equipment with protective insulation (Protecting Class II), and may be installed as fixed or freely suspended or free movable, indoor or outdoor. Installation is also possible in ducts and pipes.

TECHNICAL DATA

| | |
|--|--|
| Standards | EN 50618 IEC 62930 |
| Rated voltage | 1,5/1,5 kV DC 1,0/1,0 kV AC |
| Max. permissible operating voltage | 1,8 kV DC 1,2 kV AC |
| Test voltage (5 min) | 15 kV DC 6,5 kV AC |
| Max. conductor operating temperature | 90 °C (120 °C for 20,000 hours) |
| Max. short circuit temperature of the conductor | 250 °C (5s) |
| Operation temperature | -40 °C to +90 °C |
| Fire behavior | Flame retardant per EN IEC 60332-1-2 Annex A Low smoke emission per EN IEC 61034-2 Halogen free per EN 50525-1 and IEC 62821-1 Annex B |

DESIGN & CONSTRUCTION

1 CONDUCTOR

Flexible tinned copper conductor Class 5 according to IEC 60228

2 INSULATION

Halogen free cross-linked compound

3 OUTER SHEATH

Halogen free cross-linked compound. Color: Black (red, blue and other colors available upon request)



03/2019



Industrial Specialties - Solar

Photovoltaic Cable

PRYSUN™

TECHNICAL CHARACTERISTICS

Chemical Parameters

| | | |
|---------------------------------|--|---|
| Reaction to Fire | Fire Performance | Vertical flame propagation on complete cable per IEC 60332-1-2, EN 60332-1-2 Halogen-free per IEC 62821-1 Annex B , EN 50525-1 Annex B Low Smoke Emission per IEC 61034-2, EN 61034-2 (Light Transmittance > 60%) |
| | Construction Product Regulation (CPR) | Upon request or where applicable, CPR reaction to fire acc. to EN 50575. Euroclass: Eca |
| Weather Resistance | Weather Resistance | Ozone resistance per IEC 62930 Tab.3 per IEC 60811-403, EN 50618 Tab.2 per EN 50396 Test Type B Weathering/UV resistance on sheath per IEC 62930 Annex E and EN 50618 Annex E |
| | Acid and Alkaline Solution Resistance | Acc. IEC 62930 Annex B, EN 50618 Annex B : 7 days, 23° C (N-Oxalic Acid, N-Sodium Hydroxide) per IEC 60811-404, EN 60811-404 |
| DC Stability | Long Term Resistance of Insulation to DC | Acc. IEC 62821-2, EN 50395-9 (240h/85°C water/ 1.8kV DC) |
| Environmentally Friendly | Environmentally Friendly | PRYSUN cables comply with the RoHS Directive 2011/65/EU of the European Union |

Mechanical and Thermal Parameters

| | | |
|---|--|---|
| Operating Temperature of the Conductor | Maximum Operating Temperature of the Conductor | Acc. IEC 62930 and EN 50618: the cables are designed to operate at a normal continuous maximum conductor temperature of 90 °C. 20,000 h in operation at maximum conductor temperature of 120 °C are permitted. |
| | Resistance to Cold | Bending and Elongation at -40 ° C temperature acc. IEC 62930 Tab.2 per IEC 60811-504 and -505, acc. EN 50618 Tab2 per EN 60811-1-4 and EN 60811-504 and -505. Cold Impact Test at -40 ° C temperature acc. IEC 62930 Annex C per IEC 60811-506, acc. EN 50618 Annex C per EN 60811-506 |
| Damp-Heat | Damp-Heat Test | Meets IEC62930 Tab.2 and EN 50618 Tab.2 1.000 h at 90 ° C and 85% humidity per IEC 60068-2-78, EN 60068-2-78 |
| | Shrinkage Test on Sheath | Acc. IEC 62930 Tab. 2 per IEC 60811-503, acc. EN 50618 Tab. 2 per EN 60811-503 (Max Shrinkage 2%) |
| Mechanical and Printing | Dynamic Penetration Test | Acc. IEC 62930 Annex D, acc. EN 50618 Annex D |
| | Durability of Print | Acc. IEC 62930 , EN 50396. |

CONTACT INFO:
solar@prysmiangroup.com

03/2019