



D17a: UC^{FIBRE™} zip cord 1.8 mm x 2

Assembly cable with 2 ES9 buffered fibres, aramid yarn, FireRes[®] sheath. VDE: J-V(ZN) H 2



Application and installation

Fits small form factor connectors e.g. MTRJ connector
This cable features Draka's ES9 easy strippable tight buffer
Patch cord cable
Internal wiring

Standards

EN 187 000, IEC 60794-2, IEC 60794-2-10, ISO 11801 2nd edition, EN 50 173-1

Flame resistance

LSHF-FR (FRNC): IEC 60332-1; IEC 60332-3-24; IEC 60754-2; IEC 61034

Construction

Fibre	2 ES9 easily strippable tightly buffered fibres 900 µm ± 50 µm	
Fibre colours	Fibre 1 Natural	
	Fibre 2 Blue	
Strength member	Ultra high modulus aramid yarns	
Sheath	Halogen free, flame resistant thermoplastic sheathing compound acc. to EN 50290-2-27, UV stabilised	
Sheath colours	Cable with SM fibres	Yellow, RAL 1021
	Cable with MaxCap-BB-OM2 fibers	Orange, RAL 2003
	Cable with M6 fibres	Grey, RAL 7037
	Cable with MaxCap-BB-OM3 and MaxCap-BB-OM4 fibres	Aqua, RAL 6027
Sheath marking	Draka UC ^{FIBRE} I T N LSHF-FR ES9 1.8 2<Fibre type><Fibre brand><Item No>05<Batch Number><Meter mark> J-V(ZN)H 2 <Fibre family> <Mode field diameter> /125 <Transmission Class>	

D17a: UC^{FIBRE™} zip cord 1.8 mm x 2

Physical properties

IEC 60794-1-2

Attribute	Method	Limits
Nominal dimensions	-	1.8 mm x 3.7 mm
Nominal weight	-	6 kg/km
Tensile strength (dynamic)	E1	240 N
Tensile strength (permanent)	E1	120 N
Compressive strength (crush)	E3	600 N (max. variation 0.05 dB) 1000 N (max. variation 0.5 dB)
Impact	E4	2 Nm
Torsion	E7	5 cycles ± 1 turn
Min. Bending radius	E11	R = 20 mm
For version with BendBright ^{XS} fibre: Min. Bending radius	E11	R = 7.5 mm R = 15 mm, 6 turns around a mandrel ø 30 mm (maximum attenuation increase ≤ 0.02 dB at 1550 nm). Maximum attenuation increase for R = 10 mm 0.1 dB/turn at 1550 nm. Maximum attenuation increase for R = 7.5 mm 0.5 dB/turn at 1550 nm.
Temperature range	F1	Operation and installation: -40°C to 70°C. Storage: -40°C to 70°C
Heat of combustion	-	136 MJ/km 0.04 kWh/m

Product codes – ordering information

Prysmian Group material code	Prysmian Group material description	Draka material code	Fibre count	Fibre type	Fibre data sheet
	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 OM2B		2	OM2 MaxCap-BB-OM2	C34
	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 OM3B		2	OM3 MaxCap-BB-OM3	C31
60019842	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 OM4B	1025778	2	OM4 MaxCap-BB-OM4	C32
	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 MM61		2	OM1 62.5/125 multi mode	C02
	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 SM2D.P		2	OS2 Single mode	C18e
	UC ^{FIBRE™} I T N LSHF-FR ES9 1.8 2 SM7B		2	BendBright ^{XS} G.657. A2	C24

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group; any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.