





## Low temperature airframe wires (200°C) ASNE0261CF-U Series

| Draka Fileca part number | Conductors         |               | Gauge AWG | Ø O.D.    |           | Nominal weight (g/m) | Rating (Amp) | Conductor resistance maxi 20°C (Ω/km) |
|--------------------------|--------------------|---------------|-----------|-----------|-----------|----------------------|--------------|---------------------------------------|
|                          | Stranding (n x mm) | Section (mm²) |           | mini (mm) | maxi (mm) |                      |              |                                       |
| F E 0261CF26-U           | 19 x 0,10          | 0,15          | 26        | 0,75      | 0,84      | 1,85                 | 3            | 160                                   |
| F E 0261CF24-U           | 19 x 0,12          | 0,21          | 24        | 0,85      | 0,94      | 2,52                 | 4            | 114                                   |
| F E 0261CF22-U           | 19 x 0,15          | 0,34          | 22        | 0,98      | 1,09      | 3,74                 | 6,5          | 60                                    |
| F E 0261CF20-U           | 19 x 0,20          | 0,6           | 20        | 1,22      | 1,34      | 6,32                 | 11           | 33,2                                  |
| F E 0261CF18-U           | 19 x 0,25          | 0,93          | 18        | 1,45      | 1,59      | 9,50                 | 16           | 21,1                                  |
| F E 0261CF16-U           | 19 x 0,30          | 1,34          | 16        | 1,7       | 1,84      | 13,41                | 22           | 14,5                                  |
| F E 0261CF14-U           | 37 x 0,25          | 1,82          | 45        | 1,93      | 2,10      | 17,88                | 30           | 10,9                                  |
| F E 0261CF12-U           | 37 x 0,32          | 2,98          | 12        | 2,41      | 2,60      | 28,75                | 40           | 6,8                                   |
| F E 0261CF10-U           | 61 x 0,32          | 4,91          | 10        | 3,03      | 3,25      | 47,20                | 54           | 4,1                                   |

### REMARK

|                       |                            |                            |
|-----------------------|----------------------------|----------------------------|
| ● Breaking strength   | <u>AWG 26</u><br>> 4,6 daN | <u>AWG 24</u><br>> 6,7 daN |
| ● Stretching strength | > 6 %                      | > 6 %                      |

### CORES COLORS

- All gauges are white
- ExCept gauge 22 is light green

Passing and / or copying of this document, use or communicate of its content is not permitted without prior authorization. Information subject to change without notice.



**Draka Fileca**  
Member of Draka France