


# RadHard 62.5/125 µm Multimode Fibre (MIL-PRF-49291/6)

Legacy radiation hardened 62.5 µm MMF for irradiative environments

**Product Type:** Legacy RadHard 62.5 µm GI-Multimode Fibre (MIL-PRF-49291/6)  
**Coating Type:** Dual Layer Primary Coating (DLPC9)

**Issue date:** 04-2013  
**Supersedes:** 01-2013



This **DrakaElite™ RadHard 62.5 µm core diameter multimode fibre (MMF)** can be used for high irradiative environments (e.g. gamma rays, X-flash, neutrons protons) up to a dose of about 10 kGy. For extreme irradiative environments (some MGy dose) **DrakaElite™ Super RadHard 50 µm core diameter MMF** is recommended.  
Note: 1 Gy = 100 Rad.

This Germanium-doped **62.5 µm core diameter RadHard MMF** has been qualified and approved by the U.S. Defense Supply Center, Columbus (DSCC) in accordance with the U.S. Military **MIL-PRF-49291/6** specification.

Because Radiation Induced Attenuation (RIA) is a strong function of time after dose, dose rate, temperature, system operational wavelength, and system operational power, assessing the RIA performance of fibres should be conducted as close to conditions in the final application as possible.


The **DrakaElite™ 62.5 µm core diameter RadHard MMF** can be used in all cable constructions, including loose tube, tight buffered, ribbon and central tube designs. This fibre complies with or exceeds IEC 60793-2-10 category A1b Optical Fibre Specification, TIA-492AAAA and Telcordia GR-20-Core.

Prysmian Group' fibre plant **Draka Comteq Fibre B.V. in Eindhoven**, Netherlands, is **MIL-STD-790** certified.

Features	Advantages
RadHard behaviour	• Suitable for medium irradiative environments
Coated with the dual layer UV Acrylate	• Optimized performance in tight-buffer cable applications

Steady state gamma irradiation test conditions – MIL 49291-6		
Temperature	Dose rate	Total dose
- 28°C / 25°C / 85°C	0.50 Gy/s (SiO2)	Classified

Irradiation test requirements – MIL 49291-6		
Max. induced attenuation @1300nm	Attenuation at specified recovery time	Specified recovery time
< 50 dB/km (Total dose classified)	< 15 @ -28 °C < 5 @ 25 °C < 5 @ 85 °C	1000 s



Typical RIA for Draka RH 62.5 µm MMF at 1300nm; dose rate 1.67Gy/s, T=28°C



## RadHard 62.5/125 µm Multimode Fibre (MIL-PRF-49291/6)

Legacy radiation hardened 62.5 µm MMF for irradiative environments

**Product Type:** Legacy RadHard 62.5 µm GI-Multimode Fibre (MIL-PRF-49291/6)  
**Coating Type:** Dual Layer Primary Coating (DLP9C)

**Issue date:** 04-2013  
**Supersedes:** 01-2013

Characteristics	Conditions	Specified Values	Units
<b>OPTICAL SPECIFICATIONS (Uncabled fibre)</b>			
Attenuation Coefficient	850 nm 1300 nm	≤ 3.0 ≤ 0.7	dB/km
Overfilled Modal Bandwidth (min.) <sup>1</sup>	850 nm 1300 nm	300 600	MHz.km
RML Bandwidth (min.) <sup>1</sup>	850 nm 1300 nm	385 700	MHz.km
Numerical Aperture		0.275 ± 0.015	
Chromatic Dispersion			
Zero Dispersion Wavelength, λ <sub>0</sub>		1320 ≤ λ <sub>0</sub> ≤ 1365	nm
Zero Dispersion Slope, S <sub>0</sub>	1320 nm ≤ λ <sub>0</sub> ≤ 1348 nm 1348 nm ≤ λ <sub>0</sub> ≤ 1365 nm	≤ 0.11 ≤ 0.001 (1458 - λ <sub>0</sub> )	ps/nm <sup>2</sup> .km
Bending Loss	100 turns, D=75 mm; 850nm / 1300nm	≤ 0.5	dB
Backscatter Characteristics <sup>2</sup>			
Point Discontinuity <sup>3</sup>	850 nm, 1300 nm	≤ 0.1	dB
Irregularities over fibre length	850 nm, 1300 nm	≤ 0.1	dB
Reflections		Not allowed	
Group Index of Refraction (Typ.)	850 nm 1300 nm	1.496 1.491	
<b>GEOMERICAL SPECIFICATIONS</b>			
Core Diameter		62.5 ± 2.5	µm
Core Non-Circularity		≤ 5	%
Core/Cladding Concentricity Error		≤ 1	µm
Cladding Diameter		125.0 ± 1.0	µm
Cladding Non-Circularity		≤ 0.7	%
Coating Diameter	M49291/6-03   M49291/6-05	242 ± 10   500 ± 15	µm
Coating Non-Circularity	M49291/6-03   M49291/6-05	≤ 5   ≤ 5	%
Coating/Cladding Concentricity Error	M49291/6-03   M49291/6-05	≤ 10   ≤ 20	µm
Length	Standard lengths	2.2 – 8.8   1.1 – 6.6	km
<b>MECHANICAL SPECIFICATIONS</b>			
Coating Strip Force	Average strip force, unaged and aged <sup>4</sup> Peak strip force, unaged and aged <sup>4</sup>	1 to 3 1.8 to 13.2	Not. Spec. N
Proof Test	Off line	> 0.7 (100)	GPa (kpsi)
Dynamic Tensile Strength (median value)	0.5 meter gauge length, unaged and aged <sup>5</sup>	> 3.8 (550)	GPa (kpsi)
Fatigue Parameter (Typical)	Dynamic fatigue, unaged and aged <sup>5</sup>	n <sub>d</sub> > 18	
<b>ENVIRONMENTAL SPECIFICATIONS</b>			
Temperature Cycling	850 nm, 1300 nm; -60°C to +85°C	≤ 0.2	dB/km
Temperature-Humidity Cycling	850 nm, 1300 nm; -10°C to +85°C, 4-98% RH	≤ 0.2	dB/km
Water Immersion	850 nm, 1300 nm; 23°C, 30 days	≤ 0.2	dB/km
Dry Heat	850 nm, 1300 nm; 85°C, 30 days	≤ 0.2	dB/km
Damp Heat	850 nm, 1300 nm; 85°C; 85% RH, 30 days	≤ 0.2	dB/km
Operating Temperature Range		-55 to +85	°C
Non-Operating + Storage Temperature Range		-62 to +85	°C
<b>TYPICAL RADIATION INDUCED ATTENUATION (RIA)</b>			
Radiation Induced Attenuation	Dose: 10 KGy; Dose rate: 1.67 Gy/s; T=28°C; 1300nm	~7	dB/100m

- 1). The modal bandwidth is linearly normalized to 1 km, according to IEC 60793-2-10.
- 2). OTDR measurement with 0.5 µs pulse width.
- 3). Mean of bi-directional measurement.
- 4). Aging at 23°C, 0°C and 45°C; 30 days at 85°C and 85% RH; 14 days water immersion at 23°C.
- 5). Aging at 85°C, 85% RH, 30 days.

