


G07c: UC^{FIBRE™} Outdoor stranded loose tube cable

Stranded loose tube cable with up to 312 fibres, black PE sheath; orange PA oversheath. VDE A-DQ2Y 4Y



Application and installation

This cable can be used for a wide range of outdoor applications among them: Outdoor data communication connections, telecom trunk lines, telecom access and distribution lines and CATV trunk lines.

The low friction coefficient of the PA surface gives greatly improved flooding distances during flooding of cables into ducts. In addition improved blowing distances are obtained. The hard surface of the PA 12 jacket gives the cable a degree of rodent protection, effective in many cases. PA 12 is halogen free.

Standards

EN 187 000, IEC 60794-3, IEC 60794-3-10, IEC 60794-3-12, ISO 11801 2nd edition, EN 50 173-1

Options

As standard this cable is provided with 12 fibres per tube, as an option other lower fibre counts are possible

G07c: UC^{FIBRE™} Outdoor stranded loose tube cable

Construction

Central strength member	ø2.5 mm FRP rod		
Fibre colour code	1 Red	7 Brown	
	2 Green	8 Violet	
	3 Blue	9 Turquoise	
	4 Yellow	10 Black	
	5 White	11 Orange	
	6 Grey	12 Pink	
Loose tube	ø2.3 mm jelly filled loose tubes, with 2 – 12 fibres each, up to 26 tubes in two layers, for lay-up refer to B04		
Water blocking	The core is water blocked using swellable tape and yarn		
Wrapping	Swellable tape		
Ripcord	Polyester ripcord for easy slitting the sheath		
Sheath	1.5 mm black MDPE, IEC 60811, IEC 60708		
Oversheath	0.5 mm orange PA 12		
Sheath marking	Draka UCFIBRE O ST D DA PE PA 1.8 kN <Fibre count> <Fibre type><Fibre brand> <Item No>05<Batch Number><Meter mark> A- DQ-2Y4Y <Number of Elements> x <Fibre count per element> <Fibre family> <Mode field diameter> /125 <Transmission Class>		

Physical properties

Attribute	IEC 60794-1-2 Method	Limits							
		72	96	120	144	168	216	264	312
Fibre count		72	96	120	144	168	216	264	312
Nominal diameter [mm]		11.5	13.0	14.5	16.0	17.5	16.0	18.0	19.5
Nominal weight [kg/km]		105	135	170	205	245	205	260	270
Short term tensile strength (some days) [N]	E1	1800 N							
Permanent tensile strength [N]	E1	1200 N							
Crush (compressive strength) [N/100 mm]	E3	3000N							
Impact [J]	E4	20 Nm							
Torsion	E7	5 cycles ± 1 turn							
Kink	E10	The cables do not form a kink when a loop is drawn together to a diameter 12 times the cable nominal diameter							
Minimum bending radius [mm]	E11	170	195	220	240	260	240	270	300
Temperature range	F1	Operation *) and Installation -40 °C to 70 °C Storage -40 °C to 70 °C							
Water penetration	F5	No water on free end							

*) The cable can bear temperature cycling between -40 °C to 70 °C. The cable will operate without any attenuation variation (<0.05 dB) in the temperature range -30 °C to 60 °C. The cable will operate with a maximum attenuation variation of ±0.1 dB/km in the interval -40 °C to 70 °C

G07c: UC^{FIBRE™} Outdoor stranded loose tube cable

Product codes – ordering information

Prysmian group material code	Prysmian Group material description	Draka Material code	Fibre count	Fibre type	Fibre data sheet
60020507	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 24 SM2D	1028730	24	OS2 Single mode G652.D	C06e
60020839	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 48 SM2D	1026331	48	OS2 Single mode G652.D	C06e
60020204	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 72 SM2D	1027157	72	OS2 Single mode G652.D	C06e
60020205	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 96 SM2D	1027158	96	OS2 Single mode G652.D	C06e
60019466	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 144 SM2D	1022049	144	OS2 Single mode G652.D	C06e
60020789	UC ^{FIBRE} O ST D DA PE PA 1.8 kN 288 SM2D	1020734	288	OS2 Single mode G652.D	C06e

© PRYSMIAN GROUP 2010, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.