


LONAK[®] 2x2x0.65

Building automation cable



Application

Fixed indoor installations
LON cabling
Building automation

Flame Resistance

IEC 60332-1

Construction

Conductor	Copper wire, tinned 0.34 mm ² , Ø 0.65 mm
Insulation	PE, 1.55 mm Ø
Conductor identification	Pair 1: white, blue, Pair 2: white, orange
Stranding	2 conductors to the pair
Cable lay up	2 pairs to the core
Wrapping	1 x PET foil
Overall shielding	Laminated AL-foil + copper drain wire
Rip cord and identification thread	yes
Outer sheath	PVC, grey RAL 7035, Ø 7.1 mm
Marking	DRAKA LONAK 2x2x0.65, batch number and meter marking

Mechanical Properties

Operating temperature	- 30 °C up to + 70 °C
Min. Installation temperature	- 5 °C
Minimum bending radius	10 x D
Minimum bending radius (during pulling)	15 x D
Maximum pulling force	65 N

Electrical Properties

at 20°C

Loop DC resistance (max.)	106 Ω/km
Insulation resistance (at 500 V, 1 min.)	100 MΩ*km
Mutual capacitance at 800 Hz (max.)	49 nF/km
Velocity factor	0.67
Resistance unbalance (max.)	3 %
Capacitance unbalance (max.)	1600 pF/m
Max. operating voltage DC	75 V
Test voltage conductor/conductor	2 kV DC, 1 min.

LONAK[®] 2x2x0.65

Test voltage conductor/screen

2 kV DC, 1 min.

LONAK[®] 2x2x0.65

Technical Data

Part no. SAP	Type	Dimension	Outer diameter mm	Standard length m	weight kg/km	Copper content
1003579 CS2638100 L432911	LONAK 2x2x0.65 PVC	2x2x0.65 mm	7.1	1000	43	16.5

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2009, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.