



# N08: UC<sup>FIBRE™</sup> Universal Stranded Loose Tube Non-Metallic Gel-Filled Dca 5kN Cable

5000N, universal water-blocked stranded loose tube cable with up to 288 fibres, glass yarn reinforcement and FireRes<sup>®</sup> sheath. VDE: U-DQ(ZN)BH



12 – 72 Fibres

96 Fibres

108 - 288 Fibres



## Application and Installation

Universal indoor/outdoor cable for LAN, MAN and WAN backbones

Degree of rodent protection, effective in many cases

With its FireRes<sup>®</sup> LSHF-FR sheathing this cable is ideal for mixed indoor and limited outdoor installation. It is equally suited for installation in ducts and on trays.

## Standards

IEC 60794-1, IEC 60794-2, ISO 11801-1, EN 50173-1, EN 50575

## Flame Resistance

LSHF (FRNC): IEC 60332-1-2; IEC 60332-3-24; IEC 60754-1; IEC 60754-2; IEC 61034; EN 50399 Class D<sub>cas1d1a1</sub>; Class E<sub>ca</sub>

# N08: UC<sup>FIBRE™</sup> Universal Stranded Loose Tube Non-Metallic Gel-Filled Dca 5kN Cable

## Construction

Central strength member	ø2.5 mm FRP rod		
Lose tube	For ≤ 144 fibres, ø2.3 mm gel-filled loose tubes, with 12 fibres each For > 144 fibres, ø2.8 mm gel-filled loose tubes, with 24 fibres each for lay-up refer to B04		
Water blocking	The core is water blocked using swellable tape and tread		
Wrapping	Polyester nonwoven		
Reinforcement	Layer of glass fibre yarns as reinforcement and rodent protection		
Ripcord	Polyester ripcord for easy slitting of the sheath		
Sheath	1.5 mm FireRes® sheath, halogen free, flame retardant, UV stabilised, IEC 50290-2-27		
Cable Sheath colours	Cable with SM fibres: BendBright <sup>XS</sup> G.657.A2, BendBright G.657.A1	Yellow, RAL 1018	
	Cable with mixed fibre types (hybrid)	Blue, RAL 5015	
	Cable with OM1	Grey, RAL 7037	
	Cable with MaxCap-BendBright-OM2	Orange, RAL 2009	
	Cable with MaxCap-BendBright-OM3	Aqua, RAL 6027	
	Cable with MaxCap-BendBright-OM4	Erika-Violet, RAL 4003	
Sheath marking	Cable with BendBright WideCap-OM5	Lime-Green	
	DRAKA UC <sup>FIBRE</sup> I/O ST LSHF-FR Dca-s1-d1-a1 5.0 kN <Fibre count><Fibre type><Fibre brand> <Item No><Factory No><Batch Number><Meter mark> U-DQ(ZN)BH <Number of Elements> x <Fibre count per element> <Fibre family> <Mode field diameter> /125 <Transmission Class>		

## Physical Properties

Attribute	IEC 60794-1-21/22 Method	Limits							
Fibre count	-	12	24	36	48	72	96	144	288
Fibre Distribution		1x12f	2x12f	3x12f	4x12f	6x12f	8x12f	12x12f	12x24f
Nominal diameter [mm]	-	11.2	11.2	11.2	11.2	11.2	12.8	15.6	18.5
Nominal weight [kg/km]	-	117	120	125	127	137	167	257	
Short term tensile strength [N]	E1	5000 (fibre strain ≤ 0.6%)							
Permanent tensile strength [N]	E1	1800 (fibre strain ≤ 0.2%)							
Crush (compressive strength) [N/100 mm]	E3	2500							
Impact [J]	E4	15							
Torsion	E7	5 cycles ± 1 turn							
Kink	E10	The cables do not form a kink when a loop is drawn together to a diameter of 12 times the cable nominal diameter							
Minimum Installation bending radius (loaded) [mm]	E18a	224	224	224	224	224	256	312	370
Minimum Permanent bending radius (unloaded) [mm]	E11	112	112	112	112	112	128	156	185
Temperature range	F1	Installation				-40 °C to 70 °C			
		Operation *)				-40 °C to 70 °C			
		Storage				-40 °C to 70 °C			
Water penetration	F5	No water on free end							

\*) The cables will operate without any attenuation variation (≤0.05 dB) in the temperature interval -30°C to +60°C. The cables will operate with a maximum attenuation variation of 0.1dB/km in the temperature interval -40°C to +70°C.

# N08: UC<sup>FIBRE</sup>™ Universal Stranded Loose Tube Non-Metallic Gel-Filled Dca 5kN Cable

## Product Codes

Product Code	DoP Number*	Product Description	Fibre Count	Fibre Type	Fibre Data Sheet
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 1x12 OM3B AQ	12	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 4x12 OM3B AQ	48	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 5x12 OM3B AQ	60	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 6x12 OM3B AQ	72	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 8x12 OM3B AQ	96	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x12 OM3B AQ	144	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x24 OM3B AQ	288	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 3x12 OM4B 4003	36	MaxCap-BB-OM4	C32
60074972	1008303	UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 4x12 OM4B 4003	48	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 6x12 OM4B 4003	72	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 8x12 OM4B 4003	96	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x12 OM4B 4003	144	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x24 OM4B 4003	288	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 3x12 OM5B LG	36	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 4x12 OM5B LG	48	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 6x12 OM5B LG	72	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 8x12 OM5B LG	96	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x12 OM5B LG	144	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x24 OM5B LG	288	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 1x12 SM7A1 YL	12	OS2 BendBright G.657.A1	C17
60079564	1009670	UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 2x12 SM7A1 YL	24	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 3x12 SM7A1 YL	36	OS2 BendBright G.657.A1	C17
60081655	1009960	UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 4x12 SM7A1 YL	48	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 5x12 SM7A1 YL	60	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 6x12 SM7A1 YL	72	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 8x12 SM7A1 YL	96	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x12 SM7A1 YL	144	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x24 SM7A1 YL	288	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 1x12 SM7B YL	12	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 2x12 SM7B YL	24	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 3x12 SM7B YL	36	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 4x12 SM7B YL	48	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 6x12 SM7B YL	72	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 8x12 SM7B YL	96	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x12 SM7B YL	144	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O ST LSHF-FR 5.0kN 12x24 SM7B YL	288	OS2 BendBright <sup>XS</sup> G.657.A2	C24

\*DoP Numbers are per product code and any DoP number proves CPR approval for the cable. DoP files can be downloaded from the website: [www.prysmiangroup.com/cpr](http://www.prysmiangroup.com/cpr)

© PRYSMIAN GROUP 2017, All Rights Reserved  
 All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.  
 The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.