


# ICS PB DP BASIC 1x2xAWG22/1 LSHF

## PROFIBUS DP Basic LSHF Cable



### Application

Installation cable :

- Halogen free and flame resistant
- Limited segment length (according to PROFIBUS-Net Manual)
- UV-resistant
- Silicon free
- Limited oil and grease resistance

### Standards

Customer specification

EN 50170 part 8-2, cable type A, IEC 61158 and IEC 61784

### Flame Resistance

LSHF: IEC 60332-1, IEC 61034-2, IEC 60754-1/2

LSHF-FR: IEC 60332-3-24, IEC 61034-2, IEC 60754-1/2

### Construction

Conductor	Bare copper wire, $\varnothing$ 0.64 mm, (cross-section 0.32 mm <sup>2</sup> )
Insulation	foam-skin-PE, $\varnothing$ 2.5 mm
Stranding	two cores gn / rd to the pair and two fillers
Wrapping	PET-Foil, $\varnothing$ 5.2 mm
Static screen	PET-Al-Foil longitudinally applied
Braid	tinned copper braid, coverage approx. 60%
Sheath	halogen free, flame retardant thermoplastic sheathing compound acc. to EN 50290-2-27, $\varnothing$ 8.0 mm
Colour	violet RAL 4005
Marking	DRAKA ICS PB DP BASIC 1x2xAWG22/1 FRNC, batch number and meter marking

## ICS PB DP BASIC 1x2xAWG22/1 LSHF

### Mechanical properties

Bending radius	single bending repeated bending	≥ 60 mm ≥ 80 mm
Temperature range	Transport and storage Installation	- 25°C to + 80°C - 25°C to + 80°C - 25°C to + 80°C

### Electrical properties

at 20°C

Loop resistance	≤ 110 Ω/km
Screen resistance	≤ 9,5 Ω/km
Characteristic impedance (Nominal)	150 Ω
Mutual capacitance (at 1 kHz)	ca. 28,5 nF/km
Insulation resistance	≥ 5 GΩkm
Test Voltage (DC, 1 min) Core/Core and Core/Screen	1 kV
Operating voltage (RMS)	≤ 100 V

### Electrical data

at 20°C

Frequency	Impedance (Ohm)	Attenuation (dB/100m)		
9,6 kHz	270 ± 27	≤ 0.25		
38,4 kHz	185 ± 18,5	≤ 0.4		
1 MHz				
3 MHz	150 ± 15			
4 MHz	150 ± 15	≤ 2.2		
16 MHz	150 ± 15	≤ 4.2		
20 MHz	150 ± 15	≤ 4.7		

### Technical data

Part number	Cable type DIN/VDE	Type	Product name	Outer diameter mm	Weight kg	Standard delivery length	Drum size (mm)	Gross weight kg	Copper content	Tensile force
1026560	02YS(ST)CH	1 x 2 x 0.64/2.55-150	ICS PB DP BASIC 1x2xAWG22/1 LSHF	8.0	71	1000 m	600/200/ 310 PWD*	75	22	100 N

\*PWD (Plywood Drum)