


Optical cable

For indoor and outdoor installation.

Cable design



-not to scale -

- Central Strength Member (CSM).
- Loose Tube containing fibres and filled with a suitable water tightness compound.
- Loose tubes SZ stranded around the CSM.
- Longitudinal Water Tightness: dry core with water swellable elements.
- Peripheral Strength Elements
- Ripcords
- Outer Sheath: HFFR.Black.

Features and advantages

Indoor/outdoor installation.

- Suitable for installation in buildings and tunnel backbones where zero halogen, flame retardance and low smoke emission are required.
- Those cables may be installed as well in the outside plant as inside buildings.

Static cable bending radius 15 x cable diameter

Temperature range -40°C to +70°C

Technical data

Number of fibres (x12)	≤	12	24	36	48	60	72	96	144	192	288
Cable diameter	mm	10.4	10.4	10.4	10.4	10.4	10.9	12.2	15.5	15.9	18
Cable weight	kg/km	110	110	110	110	110	120	145	225	230	290

International standards

IEC 60794; IEC 60793 ; IEC 60332-1; IEC 61034 ; IEC 60754 ;
ITU-T Rec. G.650; ITU-T Rec. G.652; ITU-T Rec. G.655; ITU-T Rec. G.656;
ITU-T Rec. G.657;

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.