


LONAK[®] 2 x 1.3 mm² ARM

Building automation cable



Application

Fixed indoor installations
LON cabling
Building automation

Flame Resistance

Construction

Conductor	Stranded copper wires, tinned 1.3 mm ² , 7x0.49 mm, Ø 1.47 mm
Insulation	PE, 2.69 mm Ø
Conductor identification	1 x white, 1 x blue
Pair stranding	2 conductors to the pair
Cable lay up	1 pair to the core
Wrapping	1 x PET foil
Rip cord and identification thread	yes
Inner sheath	PVC, grey RAL 7035, Ø 7.0 mm
Wrapping	1 x PET foil
Armouring	2 x galvanized steel tape 15x0.20 mm
Outer sheath	PE, black RAL 9005, Ø 10.3 mm
Marking	DRAKA LONAK ARM 2x1.3, batch number and meter marking

Mechanical Properties

Operating temperature	- 30 °C up to + 70 °C
Min. Installation temperature	- 5 °C
Minimum bending radius	10 x D
Minimum bending radius (during pulling)	15 x D
Maximum pulling force	130 N

LONAK[®] 2 x 1.3 mm² ARM

Electrical Properties

at 20°C

Loop DC resistance (max.)	28 Ω/km
Insulation resistance (at 500 V, 1 min.)	100 MΩ*km
Mutual capacitance at 800 Hz (max.)	72 nF/km
Velocity factor	0.67
Max. operating voltage DC	75 V
Test voltage conductor/conductor	3.5 kV

Technical Data

Part no. SAP	Type	Dimension	Outer diameter mm	Standard length m	weight kg/km	Copper content
60013680 (1003581) (L432494)	LONAK ARM 2x1.3 PE	2x1.3 mm ²	10.3 mm	1000	172	27.1

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2014, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.