



Industrial Specialties - Solar

Photovoltaic Cables

PRYSUN™

PRYSUN™ SOLAR PV Cables

PRYSUN™ solar PV cables are intended for use in photovoltaic systems at nominal voltage rating of 1,5 kV DC.

APPLICATION

PRYSUN™ solar PV cables are designed for the interconnection of various elements in photovoltaic systems, including panel interconnection, between panels and string boxes or from string boxes to the inverter. They are suitable for applications in/at equipment with protective insulation (Protecting Class II), and may be installed as fixed or freely suspended or free movable, indoor or outdoor. Installation is also possible in ducts and pipes.

TECHNICAL DATA

Standards	EN 50618 IEC 62930
Rated voltage	1,5/1,5 kV DC 1,0/1,0 kV AC
Max. permissible operating voltage	1,8 kV DC 1,2 kV AC
Test voltage (5 min)	15 kV DC 6,5 kV AC
Max. conductor operating temperature	90°C (120°C for 20,000 hours)
Max. short circuit temperature of the conductor	250°C (5s)
Operation temperature	-40°C to +90°C
Fire behavior	Flame retardant per EN IEC 60332-1-2 Annex A Low smoke emission per EN IEC 61034-2 Halogen free per EN 50525-1 and IEC 62821-1 Annex B

DESIGN & CONSTRUCTION

1 CONDUCTOR


Flexible tinned copper conductor Class 5 according to IEC 60228

2 INSULATION

Halogen free cross-linked compound

3 OUTER SHEATH

Halogen free cross-linked compound. Color: Black (red, blue and other colors available upon request)



12/2019



Industrial Specialties - Solar

Photovoltaic Cable

PRYSUN™

TECHNICAL CHARACTERISTICS

Chemical Parameters

Reaction to Fire		Vertical flame propagation on complete cable per IEC 60332-1-2, EN 60332-1-2
	Fire Performance	Halogen-free per IEC 62821-1 Annex B , EN 50525-1 Annex B Low Smoke Emission per IEC 61034-2, EN 61034-2 (Light Transmittance > 60%)
	Construction Product Regulation (CPR)	Upon request or where applicable, CPR reaction to fire acc. to EN 50575. Euroclass: Eca
Weather Resistance		Ozone resistance per IEC 62930 Tab.3 per IEC 60811-403, EN 50618 Tab.2 per EN 50396 Test Type B
	Weather Resistance	Weathering/UV resistance on sheath per IEC 62930 Annex E and EN 50618 Annex E
Chemical Resistance	Acid and Alkaline Solution Resistance	Acc. IEC 62930 Annex B, EN 50618 Annex B : 7 days, 23°C (N-Oxalic Acid, N-Sodium Hydroxide) per IEC 60811-404, EN 60811-404
DC Stability	Long Term Resistance of Insulation to DC	Acc. IEC 62821-2, EN 50395-9 (240h/85°C water/ 1.8kV DC)
Environmentally Friendly	Environmentally Friendly	PRYSUN cables comply with the RoHS Directive 2011/65/EU of the European Union

Mechanical and Thermal Parameters

Operating Temperature		Acc. IEC 62930 and EN 50618: the cables are designed to operate at a normal continuous maximum conductor temperature of 90 °C. 20,000 h in operation at maximum conductor temperature of 120°C are permitted.
	Maximum Operating Temperature of the Conductor	
Resistance to Cold Environment		Bending and Elongation at -40°C temperature acc. IEC 62930 Tab.2 per IEC 60811-504 and -505, acc. EN 50618 Tab2 per EN 60811-1-4 and EN 60811-504 and -505.
	Resistance to Cold	Cold Impact Test at -40°C temperature acc. IEC 62930 Annex C per IEC 60811-506, acc. EN 50618 Annex C per EN 60811-506
Damp-Heat		Meets IEC 62930 Tab.2 and EN 50618 Tab.2
	Damp-Heat Test	1.000 h at 90°C and 85% humidity per IEC 60068-2-78, EN 60068-2-78
Mechanical and Printing	Shrinkage Test on Sheath	Acc. IEC 62930 Tab. 2 per IEC 60811-503 and EN 50618 Tab. 2 per EN 60811-503 (Max Shrinkage 2%)
	Dynamic Penetration Test	Acc. IEC 62930 Annex D and EN 50618 Annex D
	Durability of Print	Acc. IEC 62930 and EN 50396.

CONTACT INFO:

solar@prysmiangroup.com

12/2019