


CasaLink Block Terminal (CBT) Drop Cables

Prysmian

A Brand of Prysmian Group

Product code – See tables below



DESIGN & CONSTRUCTION

- The cables are supplied on a Wooden Bobbin.
- Single fibre terminated with an SC/APC adapter
- Available in a range of lengths from 18M to 160M
- A range of cable constructions can be used
- To be used with the Casalink Block Terminal

Product Description

The CasaLink Block Terminal (CBT) Drop cables are available in various lengths using various cable designs to suit the local market. The drop cable is a single fibre design terminated at one end with an SC/APC connector, this connector is housed in a shroud and has a pulling eye to support installation. The terminated end is secured into the Casalink Block Terminal (CBT), and the unterminated end is spliced at the customer premise. You can contact your local Prysmian sales office to discuss your requirements. In addition to buying pre-terminated CBT drop cables you can also buy a termination kit that provides all the components for local termination.

Technical data


- Packing Dimensions (DxH mm): 400x180
- Packed Weight (kg): 6

CasaLink Block Terminal (CBT) Drop Cables

Cable Design – TC04715v1

DESIGN & CONSTRUCTION

- Optical fibre:** Singlemode G.657.A1.
- Strength member:** 3 x 0.32mm brass plated steel wires.
- Tube:** Thermoplastic material, containing between 1 and 12 single-mode optical fibres and filled with a suitable water tightness compound.
- Longitudinal Water Tightness:** Water swellable elements (dry core only).
- Outer Sheath:** HDPE, 2 Ripcords beneath the sheath.
- Grooves/stripes:** Indicate planes for easy sheath removal



The design above shows 12 fibre, the drop cable only contains 1 fibre.

Cable description

This loose tube optical drop cable is design for aerial and/or duct applications and is suitable for use under 11kV power cables. The cable has a break load of 1800N and a maximum aerial span length of 95M. The table below shows the ice and wind loading for this cable. The cable also has Openreach PIA approval.

Layout		Single central tube	
Loose Tube Ø	mm	2.2	
Strength member	mm	3 x 0.32mm brass plated steel wires	
Sheath thickness	mm	1.6	
Cable Diameter	mm	6.0	
Cable Weight	kg / km	32	
Max installation tension	N	1200	
Maximum breaking load	N	1800	
Min. setting diameter	mm	120	
Temperature range	°C	Installation -20 -> +60	Operation -20 -> +60

Span (mts)	Temp	Wind and Ice Conditions							
		80 km 5 mm	100 km 5 mm	80 km 10 mm	120 km 5 mm	100 km 10 mm	80 km 15 mm	120 km 10 mm	100 km 15 mm
15	-30	Green							
25	-30	Green						Red	
35	-30	Green				Red			
45	-30	Green			Red				
55	-30	Green		Red					
65	-30	Green	Red						
75	-30	Green	Red						
85	-30	Green	Red						
95	-30	Green	Red						

CasaLink Block Terminal (CBT) Drop Cables

Part Numbers for CBT Drops using cable TC04715v1

Part Number	Length	Part Number	Length
XPCSC01138	20M	XPCSC01140	30M
XPCSC01156	22M	XPCSC01157	33M
XPCSC01139	25M	XPCSC01141	35M
Part Number	Length	Part Number	Length
XPCSC01142	40M	XPCSC01144	50M
XPCSC01143	45M	XPCSC01158	55M
Part Number	Length		
XPCSC01159	160M		