

Verticasa Mini Branching Unit

Prysmian Part Numbers: See below



The Verticasa Mini Branching Unit is typically used in multi dwelling units to breakout and distribute the fibres from an in-line Verticasa cable into a drop tube, for routing to a customer premise. It has the capacity to accommodate Verticasa cables of up to 9mm in diameter. It enables a window to be cut in the cable to access the fibres, which can be spurred of into drop tubes of 3mm in diameter (8 positions) or a drop tube of 5mm in diameter (2 positions).

Features and Benefits

- Compact, low profile, wall mounted unit typically used in multi dwelling units.
- Unit manufactured from fire resistant material to UL94-V0.
- Supplied with all of the components required to secure an in-line Verticasa cable into the unit.
- Can accommodate Verticasa cables of up to 9mm in diameter.
- Can take out 8 drop tubes of 3mm in diameter or 2 drop tubes of 5mm in diameter.
- Can be supplied to accommodate drop tubes of 3mm and 5mm in diameter.
- It's possible to reduce the length of the part by removing the top section using a pair of pliers.
- Standard colour is white RAL9016. Other colours are available on request. Please contact the Prysmian sales desk.

Kit Contents

- The Verticasa Mini Branching Unit is supplied with cable ties to secure the in-line cable.

Additional Items

- None required

Part Numbers

- **XCPSC01358** – Pack of 1
- **XCPSC01431** – Pack of 30

Technical Data

- Max number of input cables: 1 in-line
- Max diameter of in-line cable (mm): 9
- Max number of 3mm drop tubes: 8
- Max number of 5mm drop tubes: 2
- Tube Retention: > 50N
- Cable Retention: > 50N
- Required space envelope (mm): (h) 71 x (w) 40 x (d) 20
- Operating temperature: -20°C to + 60°C (5 to 95% RH)
- Material: FR ABS
- Colour: White RAL 9016
- Flammability rating: UL94-V0

Logistics

- Packing Dimensions (mm): (h) 80 x (w) 50 x (d) 30
 - Packed Weight (kg): 0.015
 - Net weight (kg): 0.015
-

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2012, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.