




Draka

Type MC Power Cable

3 XHHW-2 XLPE insulated conductors / 3 bare grounds / 8 AWG to 750 KCMIL
PVC or CPE jacket / 600 volt



Applications

For use as power and control circuits in industrial plants. Type MC cable is approved for use where exposed to direct sunlight or in cable trays or directly buried and in Class I Division 2, Class II Divisions 2, Class III Divisions 1 and 2, Hazardous Locations as defined in Articles 500, 501, 502 and 503 of the National Electrical Code (NEC).

This flame-retardant cable complies with UL Tray and ICEA T-30-520 for 70,000 BTU/HR. The finished cable also passes the 210,000 BTU/HR vertical tray flame test detailed in T-29 520.

Features

1. CONDUCTORS

Bare soft copper per ASTM B 3 concentrically stranded per ASTM B 8, and wrapped when necessary with a polyester separator tape to ease insulation stripping.

2. INSULATION

High dielectric strength, flame, heat and moisture resistant crosslinked polyethylene (XLPE) rated for continuous use at 90°C wet or dry per UL 44 for XHHW-2 wire.

3. GROUNDING CONDUCTORS

Stranded copper per ASTM B3 & B8.

4. CIRCUIT IDENTIFICATION

Insulation number printed per ICEA S-73-532 Method 4 (1-ONE, 2-TWO, etc).

5. ASSEMBLY

Insulated conductors and 3 uninsulated bare grounding conductors are cabled, using non-hygroscopic fillers where necessary, to form a round compact core. The cabled core is wrapped with a binder.

6. ARMOR

Helically applied interlocked steel (25 mils) or aluminum (25 or 34 mils) armor meeting UL 1569.

7. JACKET

Abrasion, oil / chemical resistant and highly flame retardant polyvinyl chloride (PVC) or chlorinated polyethylene (CPE) jacket meeting UL 1569.

Ratings

UL Standard 44

UL Standard 1569

National Electrical Code Articles 310, 318, 334

ICEA T-29-520, T-30-520



Type MC Power Cable

3 XHHW-2 XLPE insulated conductors / 3 bare grounds / 8 AWG to 750 KCMIL / PVC or CPE jacket / 600 volt

Part Number	Conductor AWG (Stranding)	Insulation Thickness in (mm)	Ground Conductor AWG (Stranding)	Jacket Thickness in (mm)	Nominal Cable O.D. in (mm)	Approximate Cable Steel Armor Lbs/Mft (Kg/Km)	Weight Aluminum Armor Lbs/Mft (Kg/Km)
295555	8 AWG (7/0486)	.045 (1.1)	10 (7x0385)	.050 (1.3)	.78 (19.8)	550 (818)	410 (610)
295559	6 AWG (7/0612)	.045 (1.1)	8 (7x0486)	.050 (1.3)	.86 (21.8)	710 (1056)	550 (818)
295563	4 AWG (7/0772)	.045 (1.1)	8 (7x0486)	.050 (1.3)	1.00 (25.4)	970 (1443)	760 (1131)
295567	2 AWG (7/0974)	.045 (1.1)	6 (7x0612)	.050 (1.3)	1.13 (28.7)	1320 (1964)	1080 (1607)
295571	1 AWG (19/0664)	.055 (1.4)	6 (7x0612)	.050 (1.3)	1.26 (32.0)	1600 (2470)	1320 (1964)
295574	1/0 AWG (19/0745)	.055 (1.4)	6 (7x0612)	.050 (1.3)	1.35 (34.3)	1870 (2782)	1570 (2336)
295577	2/0 AWG (19/0837)	.055 (1.4)	4 (7x0772)	.050 (1.3)	1.44 (36.6)	2210 (3288)	1880 (2797)
295580	3/0 AWG (19/0940)	.055 (1.4)	4 (7x0772)	.060 (1.5)	1.63 (41.4)	2750 (4092)	2420 (3601)
295583	4/0 AWG (19/1055)	.055 (1.4)	4 (7x0772)	.060 (1.5)	1.75 (44.4)	3270 (4866)	2910 (4330)
295586	250 KCMIL (37/0822)	.065 (1.6)	4 (7x0772)	.060 (1.5)	1.89 (48.0)	3780 (5625)	3380 (5029)
295592	350 KCMIL (37/0973)	.065 (1.6)	3 (7x0867)	.060 (1.5)	2.12 (53.8)	4970 (7395)	4510 (8050)
295601	500 KCMIL (37/1162)	.065 (1.6)	2 (7x0974)	.075 (1.9)	2.44 (62.0)	6770 (10074)	6240 (9285)
295612	750 KCMIL (61/1109)	.080 (2.0)	1 (19x0664)	.075 (1.9)	2.90 (73.7)	9730 (14478)	9090 (13525)

Part numbers are for galvanized steel armor and PVC jacketed cables only.

The data herein is approximate and subject to normal manufacturing tolerances. These specifications are subject to change without notice.

Consult factory for a variety of alternate constructions for specific applications.

Draka Engineered Specialties

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | Tel +1-508-822-5444

761 Joseph E. Warner Blvd. | Taunton, MA 02780 | Tel +1-508-822-5444

One Tamaqua Blvd. | Schuylkill Haven, PA 17972 | Tel +1-570-385-4381

For sales and technical information, contact:

Draka Engineered Specialties | 1-800-233-3190 | 1-570-385-4381 | 1-570-385-1092 fax | www.drakausa.com