


UC^{FUTURE} COMPACT^{ZD} 26 Cat.7 S/FTP 4P LSHF-FR

S/FTP Data Centre Cable Cat. 7 AWG26/1



Application

IEEE 802.3: 10Base-T; 100Base-T; 10GBase-T, ISDN; xDSL
IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s

The conductor diameter is smaller compared to the standard installation cables. This leads to an increased attenuation and therefore the operating distance is reduced (60 m instead of 90 m installation cable in standard permanent link).

Standards

IEC 61156-6 work area cable
ISO/IEC 11801 2nd ed.
EN 50173-5
EN 50288-4-2

Flame resistance

PVC IEC 60332-1
LSHF-FR IEC 60332-1; IEC 60754-2; IEC 61034

Construction

Conductor	Bare copper wire, diameter 0.4 mm (AWG26/1)
Insulation	Foam skin PP, diameter 1.0 mm (+/- 0,05)
Twisting	2 cores to the pair
Pair screening	Pet-Al foil around each pair
Screen	Tinned copper braid approx. 60% coverage
Sheath	LSHF-FR orange RAL 2003
Printing	DRAKA UC ^{FUTURE} COMPACT ^{ZD} 26 Cat.7 S/FTP 4P + batch number + meter marking

Mechanical properties

Minimum bending radius	Without load	8xD
	With load	4xD
Temperature range	During operation	-20°C up to +60°C*
	During installation	10°C up to +40°C

* POE, reduce temperature range

UC^{FUTURE} COMPACT^{ZD} 26 Cat.7 S/FTP 4P LSHF-FR

Electrical properties

at 20°C

Loop resistance		≤ 280 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V _{DC} 1 min
	core/screen	1000 V _{DC} 1 min
Capacitance	800 Hz	nom. 44 nF/km
Capacitance unbalance		≤ 1600 pF/km
Mean characteristic impedance	100 MHz	100 Ω ± 5 Ω
Nominal velocity of propagation		ca. 76%
Insulation resistance	500 V	≥ 2000 MΩkm
Coupling attenuation		≥ 85 dB

Electrical Data (nominal)

acc. to Cat.7 (at 20°C)

f (MHZ)	Attenuation (dB/10m)	NEXT (dB)	PS-NEXT (dB)	ACRF (dB/100m)	PS-ACRF (dB/100m)	Return loss (dB)
1,0	0,3	90	87	80	77	23
4,0	0,6	90	87	80	77	24
10,0	1,0	90	87	80	77	25
16,0	1,3	90	87	76	73	25
20,0	1,4	90	87	74	71	25
31,2	1,8	90	87	70	67	25
62,5	2,6	90	87	64	61	23
100,0	3,2	87	84	60	57	21
125,0	3,6	85	82	58	55	20
155,5	4,0	84	81	56	53	19
175,0	4,3	83	80	55	52	19
200,0	4,6	82	79	54	51	18
250,0	5,1	81	78	52	49	18
300,0	5,6	80	77	50	47	17
450,0	6,9	77	74	47	44	17
600,0	7,9	75	72	44	41	17

UC^{FUTURE} COMPACT^{ZD} 26 Cat.7 S/FTP 4P LSHF-FR

Product order data

Product code	Designation	Type	Outer diameter mm	Fire load		Weight kg/km	Copper content kg/km	Tensile force N
				MJ/km	kWh/m			
1016781	J-09YS(St)CH	4x2x0,4 PiMF	5.7	282	0,08	33	21	100

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
UC FUTURE CZD 26 C7 S/FTP 4P	1016781	60013695	60013695

© PRYSMIAN GROUP 2011, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.