

2.2/9.3 F PE black

CATV Trunk Cable



Application

CATV cables are used in trunk lines of CATV and broadband networks between head station and subscriber termination point. They are suitable for direct buried and duct laying.

Standards

Flame resistance

Construction

Inner conductor	bare copper wire, diameter 2.2 mm
Insulation	phys. foam PE, diameter 9.3 mm
Outer conductor	copper foil under bare copper braid, diameter 10.0 mm optical coverage 54%
Sheath	PE, diameter 12.5 ± 0.2 mm black

Electrical properties

at 20°C

DC resistance	Inner conductor	4.8 Ω/km
	Outer conductor	9.0 Ω/km
Mutual capacitance		52 pF/m
Characteristic impedance		75 Ω ± 2.25 Ω
Velocity ratio		85 %
Screening factor		> 85 dB

2.2/9.3 F PE black

Electrical data

at 20°C

Attenuation (dB/100m)		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)	
10	0.9	5 – 30	> 26
50	2.0	30 – 470	> 23
100	2.9	470 – 862	> 20
200	4.2	862 – 2150	> 18
400	6.1		
862	9.2		
1000	9.9		
1350	11.5		
1600	12.6		
1750	13.6		
2150	15.3		
2550	16.7		
3000	18.2		

Technical data

Product code	Cable type	Weight kg/km	Standard delivery length m	Drum size *PWD	Copper content	Tensile force N	Bending radius mm	Storage
1002599 CK2711200	2.2/9.3 F PE	135	1000	760/470/500	61.0	475	125	outside
1002600 CK2711201	2.2/9.3 F PE	135	1000	760/470/500	61.0	475	125	outside

*PWD (Sperrholzspule)

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
2.2/9.3 PE (GC) NK-22 CN		60011462	60011462

© PRYSMIAN GROUP 2009, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.