



Draka

VFD Power Cable for Low Frequency Drives

16 AWG to 500 KCMIL / XLPE insulation • PVC jacket / 600 volt



Applications

These are three conductor, 600 volt, Variable Frequency Drive cables with cross-linked thermosetting polyethylene (XLPE) insulation, three bare grounding conductors (one in each interstice), a corrugated copper shield and an overall polyvinyl chloride (PVC) jacket. These cables are UL type TC rated.

The VFD Power Cables are designed for use with low voltage (600 volt) AC motors controlled for speed by modern PWM (pulse width modulated) inverters. These PWM inverters require properly designed power cables to prevent RF (radio frequency) electrical signals from causing stray electrical noise or malfunction of the motor.

Features

1. CONDUCTORS

Class B, soft drawn, bare copper per ASTM B3 and ASTM B8.

2. INSULATION

Heat and moisture resistant, cross-linked thermosetting polyethylene (XLPE) meeting the requirements of UL 44. The insulation is suitable for use in wet or dry locations at a conductor temperature not exceeding 90°C for normal operation. The insulation thickness is in accordance with Table 15.3 of UL 44. Single conductors pass VW-1 flame test.

3. GROUNDING CONDUCTORS

Class B stranded, soft drawn, bare copper per ASTM B3 and ASTM B8. The grounding conductor is sectioned into three equal sections.

4. CIRCUIT IDENTIFICATION

Appendix E, Method 4 of ICEA S-73-532 (NEMA WC 57). Black conductors with number print: 1-ONE, 2-TWO & 3-THREE.

5. ASSEMBLY

The insulated circuit conductors and three bare grounding conductors are cabled together with non-hygroscopic fillers as needed. The cabled core is wrapped with a binder tape. A corrugated copper shield is applied to the taped core. A PVC jacket is applied to the shielded core.

6. SHIELD

5 mil thick copper tape (10 mil for 250, 350 and 500 KCMIL versions) corrugated and longitudinally applied with a minimum overlap of 15%.

7. JACKET

Heat and moisture resistant, black polyvinyl chloride (PVC) meeting the requirements of UL 1581. The thickness is in accordance with Table 11.3 of UL 1277.

Ratings

UL Standard 44

UL Standard 1277

IEEE 1202 (70,000 BTU/HR) Flame Test

ICEA T-29-520 (210,000 BTU/HR) Flame Test

MSHA approved



VFD Power Cable for Low Frequency Drives

16 AWG to 500 KCMIL / XLPE insulation • PVC jacket / 600 volt

Part Number	Number of Conductors/Size	Uses Crouse-Hinds Terminator™ Part Number	Number of Grounds/Size	Nominal Insulation Thickness* in (mm)	Diameter Over Shield in (mm)	Nominal Cable O.D. in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
382626	3 / 16 AWG	**	3 / 18 AWG	.030 (0.7)	0.32 (8.13)	0.43 (10.9)	92 (136)
382615	3 / 14 AWG	**	3 / 18 AWG	.030 (0.7)	0.35 (8.89)	0.46 (11.7)	144 (213)
382627	3 / 12 AWG	**	3 / 18 AWG	.030 (0.7)	0.39 (9.91)	0.51 (13.0)	176 (260)
382628	3 / 10 AWG	TMC 165	3 / 16 AWG	.030 (0.7)	0.45 (11.4)	0.59 (15.0)	254 (376)
382616	3 / 8 AWG	TMC 165	3 / 14 AWG	.045 (1.1)	0.58 (14.7)	0.73 (18.5)	390 (577)
382617	3 / 6 AWG	TMC 285	3 / 12 AWG	.045 (1.1)	0.66 (16.8)	0.78 (19.8)	263 (389)
382625	3 / 4 AWG	TMC 285	3 / 10 AWG	.045 (1.1)	0.76 (19.3)	0.93 (23.6)	769 (1138)
382618	3 / 2 AWG	TMC 3112	3 / 8 AWG	.045 (1.1)	0.89 (22.6)	1.11 (28.2)	1154 (1665)
382629	3 / 1 AWG	TMC 3112	3 / 8 AWG	.055 (1.4)	1.05 (26.7)	1.28 (32.5)	1427 (2112)
382619	3 / 1/0 AWG	TMC 4140	3 / 6 AWG	.055 (1.4)	1.15 (29.2)	1.37 (34.8)	1764 (2611)
382614	3 / 2/0 AWG	TMC 4140	3 / 6 AWG	.055 (1.4)	1.21 (30.7)	1.43 (36.3)	2077 (3074)
382630	3 / 3/0 AWG	TMC 4140	3 / 4 AWG	.055 (1.4)	1.32 (33.5)	1.55 (39.4)	2599 (3847)
382620	3 / 4/0 AWG	TMC 5161	3 / 4 AWG	.055 (1.4)	1.43 (36.3)	1.66 (42.2)	3093 (4578)
382621	3 / 250 KCMIL	TMC 5161	3 / 4 AWG	.065 (1.7)	1.57 (39.9)	1.88 (47.8)	3791 (5611)
382612	3 / 350 KCMIL	TMC 6206	3 / 2 AWG	.065 (1.7)	1.81 (46.0)	2.00 (50.8)	5020 (7430)
382631	3 / 500 KCMIL	TMC 7247	3 / 1/0 AWG	.065 (1.7)	2.08 (52.8)	2.30 (58.4)	7012 (10378)

*Insulation thicknesses shown are 600 volt. 2000 volt insulation thicknesses can also be supplied as an alternative. **Part numbers to be determined.

Optional features available are: 1) Ethylene propylene rubber (EPR) insulation, 2) CPE, LSZH or TPE jacket.

The data herein is approximate and subject to normal manufacturing tolerances. These specifications are subject to change without notice.

Consult factory for a variety of alternate constructions for specific applications.

Draka Engineered Specialties

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | Tel +1-508-822-5444

761 Joseph E. Warner Blvd. | Taunton, MA 02780 | Tel +1-508-822-5444

One Tamaqua Blvd. | Schuylkill Haven, PA 17972 | Tel +1-570-385-4381

For sales and technical information, contact:

Draka Engineered Specialties | 1-800-233-3190 | 1-570-385-4381 | 1-570-385-1092 fax | www.drakausa.com