


## S-2YCY 8 x 0.23/1.50

### Coaxial SDH-Switch Board Cables acc. to Finnish specification



### Application

### Standards

acc. to Finnish specification

### Flame resistance

### Construction

Inner conductor	copperclad steel wire, bare, diameter 0.23 mm ± 0.005 mm
Insulation	PE 1.50 mm ± 0.05 mm
Outer conductor	copper braid, bare
Sheath	PVC 2.5 mm ± 0.10 mm grey
Cable lay up	8 coaxials twisted to the bundle with number printing 1-8
Wrapping	PET-foil
Sheath	PVC 11.4 mm ± 0.5 mm grey RAL 7001

## S-2YCY 8 x 0.23/1.50

### Electrical properties

at 20°C

DC resistance	Inner conductor	≤ 1000 Ω/km
Mutual capacitance		67 nF/km
Characteristic impedance		75 Ω ± 3.0 Ω
Velocity ratio		66 %
Transfer impedance	1 MHz – 30 MHz	≤ 60.0 mΩ/m
Max. operating voltage		0.750 kV
Test voltage	Inner/Outer conductor	1.5 kV <sub>DC</sub> 1 min
Insulation resistance		≥ 10 GΩ*km

### Electrical data

at 20°C

Attenuation (dB/100m)		Crosstalk (dB/100m)		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)		Frequency (MHz)	
1	≤ 2.9	0.3 – 1	≥ 60	1-100	≥ 20
2	≤ 4.1	1.0 – 30	≥ 60		
4	≤ 5.8				
10	≤ 9.0				
17	≤ 11.6				
50	≤ 17.5				
70	≤ 20.4				
100	≤ 24.5				
140	≤ 29.0				
200	≤ 35.0				
1000	≤ 76.0				

### Technical data

Product code	Designation	Type	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size KTG/ring	Gross weight kg	Copper content	Tensile force N
CS2720901	S-2YCY	8 x 0.23/1.50	11.4	155	500 ± 20	071	103	45	225

[PRODUCT CODE TABLE]

**S-2YCY 8 x 0.23/1.50**

---

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.