

2.7/7.3AF PE, 2.7/7.3AF LSHF-FR

Coaxials basing upon DIN 47264, EN 50117-1 and IEC 61196-1



Application

The radio-frequency cables described in this chapter are used in transmitter and receiver installations in radio communications as well as in the entire field of commercial radio-frequency technology and electronics.

Standards

DIN 47264, EN50117-1, IEC 61196-1

Flame resistance

acc. to IEC 60332-3-24 (only for LSHF-FR-Version)

Construction

Inner conductor	copper wire, bare, diameter 2.71 ± 0.02 mm
Insulation	Foam-PE, diameter 7.25 ± 0.10
Outer conductor	Al-PET-Al-foil + copper braid, tinned, 93% optical coverage
Sheath	PE, alternative LSHF-FR, diameter 10.3 ± 0.2
Colour	black, RAL 9005

Mechanical properties

Minimum bending radius	without load	5 x outer diameter
	with load	10 x outer diameter
Temperature	during operation	-30° C to + 70° C
	during installation	-15° C to + 55° C
Corrosivity		IEC 60754-2

2.7/7.3AF PE, 2.7/7.3AF LSHF-FR

Electrical properties

at 20°C

DC resistance	Inner conductor	3.1 Ω/km
	Outer conductor	5.5 Ω/km
Mutual capacitance		79 pF/m
Velocity ratio		84 %
Characteristic impedance at 200 MHz		50 Ω ± 2 Ω
Transfer impedance	1 MHz	≤ 5 mΩ/m
	10 MHz	≤ 4 mΩ/m
	100 MHz	≤ 2 mΩ/m
Operating voltage		1.2 kV _{rms}
Test voltage	Inner/Outer conductor	3.0 kV _{rms}
Screening factor	100-1000 MHz	≥ 90 dB
	1000-3000 MHz	≥ 80 dB
Insulation resistance		≥ 10 GΩ*km

Electrical data

at 20°C

Frequency (MHz)	Attenuation (dB/100m)	Max. power rating (Watts) (ambient temperature 40°C and max. inner conductor temperature 100°C)	Return loss (dB) several peaks are allowed	
			Frequency (MHz)	
	nominal	maximal		
1	0.4	17328	10-450	□□26
10	1.3	5480	450-1000	□□23
100	4.1	1710	1000-3000	□□18
200	5.7	1132		
500	9.3	716		
800	12.2	585		
1000	13.6	523		
1500	16.7	427		
2000	19.5	351		
2500	22.1	325		
3000	24.8	261		
3500	27.1	240		
4000	29.3	246		
5250	34.3	216		
5725	36.3	205		
6000	37.2	200		

2.7/7.3AF PE, 2.7/7.3AF LSHF-FR

Technical data

Product code	Designation	Type	Brand name	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size *PWD	Gross weight kg	Copper content	Tensile force N
1002703	02Y(St)C 2Y	2.7/7.3 AF	2.7/7.3AF PE	10.3	136	1000	760/470/ 500	150	101	505
1002762	02Y(St)C H	2.7/7.3 AF	2.7/7.3 AF LSHF-FR	10.3	145	1000	760/470/ 500	150	101	505

*PWD (Plywood drum)

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
2.7/7.3AF PE		60015137	60015137
2.7/7.3AF PE 1000DW	1002703-01000DW	60015137	60015138
2.7/7.3AF PE 40RW	1002703-00040RW	60015137	60015139

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.