


J-2YY/H 25/50/100x2x0.5

U/UTP data cable acc. to Cat. 3



Application

These cables are used as riser cable in structured cabling networks, most often between distribution frames.

Standards

IEC 61156, ISO/IEC 11801 /1995, TIA/EIA 568-A

Flame resistance

PVC IEC 60332-1
FRNC IEC 60332-1; IEC 60754-2; IEC 61034

Construction

Conductor	Solid bare copper wire, diameter 0.5 mm
Insulation	Solid PE (2Y)
Stranding	5 or 10 pairs stranded to sub units. Cables with 100 pairs are built up with 1 st layer: 3 basic units, 2 nd layer: 7 basic units
Identification	Pair 1-5: a-Core wt; b-Core bl, or, gn, br, gr Pair 6-10: a-Core rd; b-Core bl, or, gn, br, gr Sub units 1-10: color of binding tapes acc. to IEC 60304: bl, or, gn, br, gr, wt, rd, bk, ye, vi
Wrapping	Plastic foils
Sheath	FRNC (H), also available on request with PVC (Y) grey, RAL 7035

Mechanical properties

Minimum bending radius	without load	4 x D (D= outer diameter)
	with load	8 x D (D= outer diameter)
Temperature	during operation	- 20° C to + 60° C
	during installation	0° C to + 50° C

J-2YY/H 25/50/100x2x0.5

Electrical properties

at 20°C

Loop resistance		≤ 192 Ω/km
Test voltage	core/core	1500 V
	core/screen	1500 V
Capacitance unbalance	1 kHz	≤ 1500 pF/km
Characteristic impedance	1 – 16 MHz	100 Ω ± 15 Ω
Insulation resistance		≥ 5 GΩ*km

Electrical data

at 20°C

Frequency (kHz)	Attenuation (dB/km)	NEXT (Test length > 300 m) (dB)
	(nominal value)	(nominal value)
1	26	41
4	56	32
10	98	26
16	131	23

Product order data

Product code	Designation	Type	Outer diameter ca. mm	Weight ca. kg/km	Standard delivery length m	Copper content kg/km	Tensile force N
on request	J-2YY	25x2x0.5 Cat. 3	12.7	184	1000	120	500
on request	J-2YY	50x2x0.5 Cat. 3	16.1	314	1000	240	1000
on request	J-2YY	100x2x0.5 Cat. 3	21.9	590	1000	485	2000
1000062-01000DX	J-2YH	25x2x0.5 Cat. 3 FRNC	12.7	170	1000	120	500
1000063-01000DX	J-2YH	50x2x0.5 Cat. 3 FRNC	16.1	297	1000	240	1000
1000064-01000DX	J-2YH	100x2x0.5 Cat. 3 FRNC	21.9	560	1000	485	2000

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2010, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.