


S-2Y(St)Y/H 25/50/100x2x0.52 (AWG 24)

F/UTP symmetrical Data Cable acc. to Cat. 5



Application

IEEE 802.3: 10Base-T; 100Base-T; ISDN; xDSL
IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s

Standards

IEC 61156-4

Flame resistance

PVC IEC 60332-1
LSZH; LSHF IEC 60332-1; IEC 60754-2; IEC 61034

Construction

Conductor	Bare copper wire, Ø 0.52 mm (AWG24), diameter 0.52 mm (AWG24)										
Insulation	PE, diameter 0.95 mm										
Twisting	2 cores to pair, diameter 1.9 mm										
Sub unit stranding	5 pairs to subunit + filler, diameter 5.0 mm										
Main unit stranding	5 subunits to a 25" unit + filler PET foil wrapping, diameter 13.0 mm										
Identification	<table border="0"> <tr> <td>Pair 1 – 5: a-Core wt;</td> <td>b- Core bl, or, gn, br, gr</td> </tr> <tr> <td>Pair 6 – 10: a- Core rd;</td> <td>b- Core bl, or, gn, br, gr</td> </tr> <tr> <td>Pair 11 – 15: a- Core bk;</td> <td>b- Core bl, or, gn, br, gr</td> </tr> <tr> <td>Pair 16 – 20: a- Core ye;</td> <td>b- Core bl, or, gn, br, gr</td> </tr> <tr> <td>Pair 21 – 25: a- Core vi;</td> <td>b- Core bl, or, gn, br, gr</td> </tr> </table> <p>Binding tapes of main units: bl, or, gn, br</p>	Pair 1 – 5: a-Core wt;	b- Core bl, or, gn, br, gr	Pair 6 – 10: a- Core rd;	b- Core bl, or, gn, br, gr	Pair 11 – 15: a- Core bk;	b- Core bl, or, gn, br, gr	Pair 16 – 20: a- Core ye;	b- Core bl, or, gn, br, gr	Pair 21 – 25: a- Core vi;	b- Core bl, or, gn, br, gr
Pair 1 – 5: a-Core wt;	b- Core bl, or, gn, br, gr										
Pair 6 – 10: a- Core rd;	b- Core bl, or, gn, br, gr										
Pair 11 – 15: a- Core bk;	b- Core bl, or, gn, br, gr										
Pair 16 – 20: a- Core ye;	b- Core bl, or, gn, br, gr										
Pair 21 – 25: a- Core vi;	b- Core bl, or, gn, br, gr										
Screen	Al -laminated plastic foil, drain wire AWG 26, diameter 13.0 mm										
Sheath	PVC or HFFR, diameter 15.5 mm grey, RAL 7035										
Printing	DRAKA S-2Y(St)Y 25x2xAWG24 CAT5 + meter marking+ batch number										

S-2Y(St)Y/H 25/50/100x2x0.52 (AWG 24)

Mechanical properties

Minimum bending radius	without load	≥ 60 mm
	with load	≥ 120 mm
Temperature	during operation	- 20° C to + 60° C
	during installation	0° C to + 50° C

Electrical properties

at 20°C

Loop resistance		≤ 190 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V _{DC} 1 min
	core/screen	1000 V _{DC} 1 min
Mutual capacitance	800 Hz	nom. 48 nF/km
Capacitance unbalance	pair/ground	≤ 1500 pF/km
Characteristic impedance	1 – 100 MHz	100 Ω ± 15 Ω
Relative Velocity ratio		ca. 67%
Transfer impedance	1 MHz	≤ 50 mΩ/m
	10 MHz	≤ 100 mΩ/m
	30 MHz	≤ 200 mΩ/m
Insulation resistance	500 V	≥ 5000 MΩ*km

Electrical data (nominal)

at 20°C

Frequency (MHz)	Attenuation (dB/100m)	NEXT (dB)	ACR (dB/100m)	Return loss (dB)
1	1.9	71	69.1	20
4	3.7	62	58.3	23
10	6.0	56	50.0	25
16	7.6	53	45.4	25
20	8.5	51	42.5	25
31.2	10.7	49	38.3	24
62.5	15.7	44	28.3	22
100	19.8	41	21.2	20

S-2Y(St)Y/H 25/50/100x2x0.52 (AWG 24)

Technical data

Product code	Designation	Type	Outer diameter mm	Fire load		Weight kg/km	Copper content	Tensile force N
				MJ/km	kWh/m			
1003300	S-2Y(St)Y	25x2x0.52 Cat.5	15.5	2390	0.664	190	120	500
	S-2Y(St)Y	50x2x0.52 Cat.5	27.5	4802	1.056	380	240	1000
	S-2Y(St)Y	100x2x0.52 Cat.5	32.5	9640	2.677	770	485	2000
1003316	S-2Y(St)H	25x2x0.52 Cat.5 FRNC	15.5	2250	0.664	190	120	500
1014265	S-2Y(St)H	50x2x0.52 Cat.5 FRNC	27.5	4502	1.250	380	240	1000
1003317	S-2Y(St)H	100x2x0.52 Cat.5 FRNC	32.5	9520	2.644	770	485	2000

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
DR S-2Y(St)H 25x2x0.52 (AWG24)C5		60011418	60011418
DR S-2Y(St)H 50x2x0.52 (AWG24)C5		60011419	60011419
DR S-2Y(St)H 100x2x0.52 (AWG24)C5		60014765	60014765

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.