


AC10 SS 24/7 1P

Audio Cable



Application

Audio cables are used in professional broadcasting systems for the transmission of analogue and digital audio signals for mobile use.

Standards

basing upon ARD-Specification and acc. to AES/EBU-Recommendation

Flame resistance

VDE 0472 part 804 class B and IEC 332-1

Construction

Conductor	stranded copper wires, bare AWG24/7(7x0.2mm)	Ø 0.6 mm (cross section 0.22 mm ²)
Insulation	Foam-skin-PE	Ø 1.55 mm
Pair stranding	two cores twisted to the pair	Ø 3.1 mm
Pair identification	a - core: white, b - core: blue	
Pair screen	Al-PET-foil, Aluminium inside + stranded copper drain wires, tinned	Ø 3.2 mm
Pair insulation	PET-foil	
Overall screen	copper braid, tinned	
Sheath	PVC/rubber	
Sheath colour	matt black RAL 9005	
Sheath marking	DRAKA COMTEQ – AC10 SS 24/7 1P AES/EBU - 110 Ω	

Mechanical properties

Temperature range	- 30 °C bis + 70 °C	
Bending radius during installation	without load	≥ 10 x cable diameter
	with load	≥ 15 x cable diameter

AC10 SS 24/7 1P

Electrical properties

at 20°C

DC loop resistance	(at 20 ± 5 °C)	≤ 174 Ω/km
Insulation resistance (at 20 ± 5 °C and 500 V)	(at 20 ± 5 °C and 500 V)	≤ 2000 MΩxkm
Mutual capacitance at 800 Hz		nom. 45 nF/km
Capacitance unbalance (pair to ground)		Capacitance unbalance (pair to ground)
Velocity ratio		approx. 78 %
Test voltage (50 Hz, 1 min) core/core and core/screen		700 V eff.
Characteristic impedance		6 MHz : 110 Ω ± 10%
Transfer impedance		up to 10 MHz ≤ 10 mΩ/m up to 100 MHz ≤ 100 mΩ/m

Electrical data

at 20°C

Frequency		Near-end crosstalk (cable length: 300 m)	Attenuation
[MHz]		[dB]	[dB/100m]
0.015		85	0.45
1.0		85	2.4
4.0		90	4.6
10.0		90	6.7
20.0		85	8.1

Technical data

Product code	Designation	Type	Brand name	Outer dia-meter	Weight	Standard-delivery length	Drum size	Gross weight	Copper content	Tensile force
				mm	kg/km	m	EW	kg		N
1001982 CT2757601	Li- 02YSCY	1x2x0.6L PiMF	AC10 SS 24/7 1P PVC/rubber	6.0 ± 0.2	40	1000	050	40	17	60

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
AC10 SS 24/7 1P		--	60021920

© PRYSMIAN GROUP 2006, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.