

62.5 μm OM1 Multimode Fibre with 500 μm coating



Issue date: February 2022

Applicable Standards

- IEC / EN 60793-2-10: type A1-OM1
- ISO / IEC 11801: Category OM1
- TIA / EIA 492 AAAF

Optical Specifications

Bandwidth (OFL)

Attribute	Units	Specified Values
Overfilled Modal Bandwidth at 850 nm	MHz•km	≥ 200
Overfilled Modal Bandwidth at 1300 nm	MHz•km	≥ 500

Attenuation

Attribute	Units	Specified Values
Attenuation coefficient at 850 nm	dB/km	≤ 3.0
Attenuation coefficient at 1300 nm	dB/km	≤ 0.7

Numerical Aperture

Numerical aperture	0.275 ± 0.015	
--------------------	---------------	--

Macrobending Loss

Conditions	Wavelength	Units	Specified Values
Mandrel Radius = 37.5 mm, 100 Turns	850 / 1300 nm	dB	≤ 0.5 / ≤ 0.5

Chromatic Dispersion

Attribute	Conditions	Units	Specified Values
Zero Dispersion Wavelength, λ_0		nm	1320 ≤ λ_0 ≤ 1365

Backscatter characteristics ¹

Attribute	Conditions	Units	Specified Values
Point Discontinuity ²	850 nm, 1300 nm	dB	≤ 0.1
Irregularities over fibre length	850 nm, 1300 nm	dB	≤ 0.1
Reflections	-	-	Not allowed
Group Index of Refraction at 850 nm	-	-	1.496 (typical)
Group Index of Refraction at 1300 nm	-	-	1.491 (typical)

¹ OTDR measurement with 0.5 μs pulse width.

² Mean of bi-directional measurement

Geometrical Specifications

Glass Geometry

Attribute	Units	Specified Values
Core Diameter	μm	62.5 ± 2.5
Core non-Circularity	%	≤ 5
Core-Cladding Concentricity Error	μm	≤ 1.5
Cladding Diameter	μm	125 ± 1
Cladding non-Circularity	%	≤ 1

Coating Geometry

Attribute	Units	Specified Values
Coating Diameter	μm	500 ± 15
Coating non-Circularity	%	≤ 5
Coating-Cladding Concentricity Error	μm	≤ 20

Mechanical Specifications

Proof Test ³

The entire spool length is subjected to a tensile proof stress ≥ 0.7 GPa (100 kpsi) ; 1% strain equivalent

³ Higher proof test available upon request

Coating Performance

Attribute	Units	Typical Values
Average Coating Strip Force, unaged and aged ⁴	N	2
Peak Coating Strip Force, unaged and aged ⁴	N	1.3 to 8.9

⁴ Aging at 23°C, 30 days

Fibre Strength

Attribute	Units	Specified Values
Dynamic Tensile Strength (0.5 meter gauge length), unaged and aged ⁵	GPa	median > 3.8 (550 kpsi)
Dynamic Fatigue, unaged and aged ⁵	-	$n_d \geq 18$ ⁵ Aging at 85°C, 85% RH, 30 days

Environmental Specifications

Environmental test	Test Conditions	Induced attenuation at 850, 1300 nm (dB/km)
Temperature Cycling	-60°C to +85°C	≤ 0.2
Temperature - Humidity Cycling	-10°C to +85°C, 4-98% RH	≤ 0.2
Water Immersion	30 days; 23°C	≤ 0.2
Dry Heat	30 days ; 85°C	≤ 0.2
Damp Heat	30 days; 85°C; 85% RH	≤ 0.2

Others

Length	Up to 6.6 km per spool
Coating	Acrylate Coating (Clear)

All measurements in accordance with ITU-T G650 recommendations