


756-12 (756-10 modified)

Multicore Camera Cable



Application

The multicore camera cable 756-12 is used in professional video productions for simultaneous transmission of energy, video and control signals for camera systems of Philips, Sony and Ikegami.

Standards

Flame resistance

Construction

Unit 1, 6 x coaxial cable 0.38/1.7

Inner conductor	stranded copper wires, tinned, diameter 0.4 mm
Insulation	foam-PE, diameter 1.7 mm
Outer conductor	copper braid, tinned, diameter 2.1 mm
Sheath	PVC, diameter 2.6 mm
Identification	yellow, orange, green, blue, pink, brown

Unit 2, 2 x screened control core 0.14 mm²

Inner conductor	stranded copper wires, tinned, diameter 0.5 mm
Insulation	PVC, diameter 1.0 mm
Screen	copper wires, tinned, 32x0.10 mm, diameter 1.2 mm
Sheath	PVC, diameter 1.7 mm
Identification	1 x black, 1 x white

Unit 3, 2 x power core 1.5 mm²

Inner conductor	stranded copper wires, tinned, diameter 1.6 mm
Insulation	PVC, diameter 2.2 mm
Identification	1 x black, 1 x white

Unit 4, 3 x screened audio pair 2 x 0.14 mm²

Inner conductor	stranded copper wires, tinned, diameter 0.5 mm
Insulation	PVC, diameter 0.9 mm
Identification	1 x red, 1 x white
Stranding	2 cores stranded to the pair, diameter 1.8 mm
Screen	copper wires, tinned, 60x0.10, diameter 2.0 mm
Sheath	PVC, diameter 2.5 mm
Identification	1 x orange, 1 x brown, 1 x red

756-12 (756-10 modified)

Unit 5, 9 x pilot core 0.14 mm²

Inner conductor	stranded copper wires, tinned, diameter 0.5 mm
Insulation	PVC, diameter 1.0 mm
Identification	1 x red, 1 x blue, 7 x white
Cable lay up	
Stranding	
inner layer	2 x unit 3, in each inner interstice, diameter 4.8 mm 1 x unit 2
outer layer	3 x unit 4 and 6 x unit 1, diameter 10.0 mm sequence: 1 x unit 1-brown, 1 x unit 1-pink, 1 x unit 4-red, 1 x unit 1-orange, 1 x unit 1-yellow, 1 x unit 4-orange, 1 x unit 1-green, 1 x unit 1-blue, 1 x unit 4-brown, 9 x unit 5 in the outer gaps
Wrapping	1 x PETP-web, diameter 10.1 mm
Cable screen	copper braid, tinned, diameter 10.7 mm
Sheath	PVC, black RAL 9005, diameter 12.7 mm
Printing	DRAKA COMTEQ KAMERAKABEL 756-12

Electrical properties

at 20°C

Coaxial cable 0.38/1.7 - 75 Ω

DC resistance	inner conductor	230 Ω/km
	outer conductor	31 Ω/km
Mutual capacitance	1 kHz	62 ± 7 pF/m
Characteristic impedance	10 MHz	75 ± 5 Ω
Insulation resistance	at 15.6 °C	≥ 1000 MΩ*km
Test voltage		110 V _{AC}
Operating voltage		≤ 30 V _{AC}

Screened control core 0.14 mm²

DC resistance	inner conductor	129 Ω/km
	screen	72 Ω/km
Insulation resistance	at 15.6°C	≥ 0.5 MΩ*km
Test voltage	(50 Hz, 1 min) core/core/environment	110 V _{AC}
Operating voltage		≤ 30 V _{AC}

Power core 1.5 mm²

DC resistance		≤ 12.5 Ω/km
Insulation resistance	at 15.6°C	≥ 0.5 MΩ*km
Test voltage	(50 Hz, 1 min) core/core/screen	110 V _{AC}
Operating voltage		≤ 30 V _{AC}

Screened audio pair 2 x 0.14 mm²

DC resistance	inner conductor	130 Ω/km
	screen	40 Ω/km
Insulation resistance	at 15.6°C	≥ 0.5 MΩ*km
Test voltage		110 V _{AC}
Operating voltage		≤ 30 V _{AC}

Pilot core 0.14 mm²

DC resistance		129 Ω/km
---------------	--	----------

756-12 (756-10 modified)

Insulation resistance	at 15.6°C	$\geq 0.5 \text{ M}\Omega \cdot \text{km}$
Test voltage		110 V _{AC}
Operating voltage		$\leq 30 \text{ V}_{AC}$

756-12 (756-10 modified)

Electrical data

at 20°C

Coaxial cable 0.38L/1.6

Frequency (MHz)	Attenuation (dB/km)
10	79

Technical data

Product code	Type	Weight kg/km	Copper content	Standard delivery length m	Drum size KTG	Minimum bending radius mm	Tensile force N	Storage
1002366 CT2739100	756-12 PVC black	250	193.2	1000	091	130	800	inside

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
756-12 PVC		60014005	60014005

© PRYSMIAN GROUP 2006, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.