


VA12

Studio Connecting Cable



Application

Studio connecting cables are primarily used in closed circuit TV systems and for compact installations in studios and broadcasting vans. They are not suitable for continuously moved applications.

Standards

Flame resistance

Audio cable AC10 SP 24/7 nP: VDE 0472 part 804 class B and IEC 60332-1

Construction

Element 1: Coaxial cable 0.8/3.7 AF – 75 Ω

Inner conductor	solid copper, bare, diameter 0.8 mm
Insulation	Foam-PE, diameter 3.7 mm
Outer conductor	Al-PET-Al foil, under tinned copper braid, diameter 4.5 mm
Sheath	PVC, diameter 5.9 mm blue, RAL 5015

Element 2: 1 x Element from the multi audio cable AC10SP 24/7 nP

Inner conductor	stranded copper wires, bare, diameter 0.60 mm (AWG24/7) (0.22 mm ²)
Insulation	Foam-skin-PE, diameter 1.40 mm
Pair stranding	2 cores twisted to the pair
Pair identification	a - core: white, b - core: blue (the colours above in regular intervals)
Pair screen	one layer of spiraled bare copper wires + stranded bare copper drain wires, diameter 3.0 mm
Sheath	PVC, diameter 3.8 mm

Cable lay up

Stranding	(0+3) 1 x Element 1 + 2 x Element 2 + 2 x filler diameter 9.7 mm
Wrapping	1 x Polyester web, diameter 9.5 mm
Sheath	DMC FLEX PVC, diameter 11.8 mm ± 0.5 mm black, RAL 9005
Printing	DRAKA COMTEQ – VA12 + meter marking + batch number

VA12

Mechanical properties

Audio cable AC10 SP 24/7 nP

Minimum bending radius	without load	$\geq 10 \times D$ (D= outer diameter)
	with load	$\geq 15 \times D$ (D= outer diameter)
Temperature range	during operation	- 30° C to + 70° C

Electrical properties

at 20°C

Coaxial cable 0.8/3.7 AF – 75 Ω

Characteristic impedance		$75 \Omega \pm 0.5 \Omega$
Screening factor		> 100 dB
Velocity ratio		78 %
DC resistance	Inner conductor	35 Ω/km
	Outer conductor	19 Ω/km
Mutual capacitance		56 nF/km

Audio cable AC10SP 24/7 nP

DC resistance		$\leq 175 \Omega/\text{km}$
Insulation resistance	500 V	$\geq 2000 \text{ M}\Omega \cdot \text{km}$
Mutual capacitance	800 Hz	nom. 46 nF/km
Velocity ratio		78 %
Test voltage	DC. 1 min	1000 V
Characteristic impedance	6 MHz	$110 \Omega \pm 10 \%$

VA12

Electrical data Coaxial cable 0.8/3.7 AF – 75 Ω

at 20°C

Attenuation (dB/100m)		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)	
1	0.9	50 – 300	> 23
5	1.9	300 – 800	> 19
10	2.7		
100	7.9		
300	13.3		
500	17.6		
800	22.8		
1000	25.5		
1500	31.3		

Audio cable AC10SP 24/7 nP

Frequency (MHz)	Attenuation (dB/100m)	Near end crosstalk (dB/300m)	
		neighbourled pairs	unneighbourled pairs
0.015	0.3	100	100
1.0	1.5	75	85
4.0	3.8	65	80
10.0	6.0	63	70
20.0	8.5	60	65

Technical data

Product code	Type	Weight kg/km	Standard delivery length m	Drum size *PWD	Copper content	Tensile force N	Minimum bending radius N mm	Storage
1002302 CT2875700	VA12	178	1000	1000/500/5 60	45	225	120	inside

*PWD (plywood drum)

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2002, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.