


# SMPTE 311M-HD-Hybrid-Camera Cable

## Hybrid-HDTV-Camera Cable



### Application

This Hybrid HD Camera Cable 2SM 9/125 + 4 x AWG20 + 2 x AWG24 acc. to SMPTE 311M-Standard contains Single-Mode Optical Fibres, Auxiliary- and Signal Conductors. It is used in professional video productions for simultaneous transmission of energy, video, audio and control signals and is intended to interconnect Camera Units and Base Stations in conjunction with the Connector Interface Standard. It is suitable for all new digital camera systems of well-known manufacturers.

### Standards

SMPTE 311M

### Flame resistance

FRNC jacket: IEC 60332-1, IEC 60754-2, IEC 61034

### Construction

#### Element 1: Auxiliary Conductors AWG20 (4 x 0.6 mm<sup>2</sup>)

Conductor	tinned stranded copper wires, 19 x 0.20 mm, diameter 1.0 mm
Insulation	HDPE, diameter 1.5 mm
Identification	2 x black, 2 x white

#### Element 2: Signal Conductors AWG24 (2 x 0.22 mm<sup>2</sup>)

Conductor	tinned stranded copper wires, 7 x 0.20 mm, diameter 0.6 mm
Insulation	HDPE, diameter 1.1 mm
Identification	1 x red, 1 x grey

#### Element 3: Fibre Optic Single Mode (2 x 9/125µ)

Mode field diameter	at 1310 nm, diameter 9.5 µm ± 1 µm
Cladding diameter	diameter 125 µm ± 1 µm
Concentricity error	≤ 1 µm
Coating material	UV-cross-linked Acrylate, diameter 245 µm
Buffer material	Thermoplastic, diameter 0.9 µm ± 0.05 µm
Identification	1 x blue, 1x yellow

#### Element 4: Strength Member AWG16 (1 x 1.22 mm<sup>2</sup>)

Conductor	galvanized steel wires, diameter 1.6 mm
Insulation	HDPE, diameter 2.1 mm
Identification	1 x white

#### Cable lay up

Stranding	Core: 1 x Element 4, diameter 2.1 mm Layer: 4 x Element 1 + 2 x Element 2 + 2 x Element 3 and in the outer interstices 4 x fibrillated Polypropylene as needed for roundness, diameter 5.2 mm Sequence according to the above drawing
Wrapping	1 x non-woven fabric tape, diameter 5.4 mm

## SMPTE 311M-HD-Hybrid-Camera Cable

Screen	Copper wire braid, tinned 95% opt. coverage, diameter 5.9 mm
Sheath	PUR or FRNC, diameter 9.2 mm black, RAL 9005
Printing	PUR: <b>DRAKA</b> SMPTE 311 M Zero-Loss HD Cable + batch number + meter marking FRNC: <b>DRAKA</b> SMPTE 311 M Zero-Loss HD Cable FRNC + batch number + meter marking

### Mechanical properties

Temperature range PUR (FRNC)	during operation	- 40° C to + 70° C ( -25°C to +70°C)
Max. humidity		95 %

### Electrical properties

at 20°C

#### Auxiliary Conductors AWG20 (4 x 0.6 mm<sup>2</sup>)

DC resistance		≤ 35.3 Ω/km
Loop resistance		≤ 43 Ω/km
Insulation resistance		≥ 10 <sup>4</sup> MΩ*km
Test voltage		1750 V <sub>AC rms</sub>
Operating voltage		≤ 300 V <sub>AC rms</sub>

#### Signal Conductors AWG24 (2 x 0.22 mm<sup>2</sup>)

DC resistance		≤ 97.5 Ω/km
Loop resistance		≤ 184 Ω/km
Insulation resistance		≥ 10 <sup>4</sup> MΩ*km
Test voltage		1750 V <sub>AC rms</sub>
Operating voltage		≤ 300 V <sub>AC rms</sub>

#### Overall screen

DC resistance		≤ 20 Ω/km
---------------	--	-----------

### Optical properties

at 20°C

#### Fibre Optic Single Mode (2 x 9/125μ)

Cut-off wavelength		1100 – 1350 nm
Attenuation	at 1310 nm	0.5 dB
Dispersion	at 1310 nm	3.5 ps/nm*km

### Technical data

Product code	Type	Weight kg/km	Standard delivery length m	Drum size KTG	Copper content	Tensile force N	Minimum bending radius mm	Storage
1002458 CT298700 0 glossy	SMPTE 311M Hybrid Camera Cable	115	1000	081	47.2	800	65	inside
1008069 CT298700 2 dull	SMPTE 311M Hybrid Camera Cable	115	1000	081	47.2	800	65	inside
1018337 CT768700	SMPTE 311M Hybrid Camera	115	1000	081	47.2	800	90	inside

## SMPTE 311M-HD-Hybrid-Camera Cable

0	Cable FRNC						
---	------------	--	--	--	--	--	--

<

### Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
DR SMPTE 311M-HD-HYBRID 1000DW	1008069-01000DW	60014967	<b>60011292</b>
SMPTE 311M-HD-HYBRID-CAMERACABLE FRNC		60014834	<b>60014834</b>
SMPTE 311M-HD-HYBRID-CAMERACABLE FRNC		60014856	<b>60014856</b>
DR SMPTE 311M-HD-HYBRID-CAMERACABLE PU		60014967	<b>60014967</b>

© PRYSMIAN GROUP 2009, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.