


UC900 SS23 Cat.7 (L)H

S/FTP



Application

Indoor and outdoor installations in non-permanently wet conditions.
Primary (Campus), Secondary (Riser), Tertiary (Horizontal)
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T
IEEE 802.5 16 MB; ISDN; TPDDI; ATM

Standards

EN 50173-1; EN 50288-4-1
ISO/IEC 11801; IEC 61156-5

Flame resistance

LSHF(LSOH): IEC 60332-1; IEC 60754-2; IEC 61034
LSHF-FR: IEC 60332-1; IEC 60332-3-24; IEC 60754-2; IEC 61034

Construction

Conductor	bare copper wire, Ø 0.56 mm (AWG 23)
Insulation	foamskin PE, Ø 1.4 mm
Twisting	2 cores to the pair
Pair screen	Al-laminated plastic foil
Cable lay up	4 pairs (PiMF) to the core
Screen	copper braid, tinned
Sheath: LSHF	Aluminum tape laminated to the inside of the sheath LSHF (LSOH), black, wall thickness 1.5 mm
Sheath: LSHF-FR	Alternative: Aluminum tape laminated to the inside of the sheath LSHF-FR (LSOH-FR), black, wall thickness 1.5 mm

Mechanical properties

Bending radius	without load	≥ 40 mm
	with load	≥ 80 mm
Temperature range	during operation	-20°C to + 60°C
	during installation	0°C to + 50°C

UC900 SS23 Cat.7 (L)H

Electrical properties

at 20°C ± 5°C

Loop resistance		≤ 165 Ω/km
Resistance unbalance		≤ 2%
Insulation resistance	(500 V)	≥ 5000 MΩ*km
Mutual capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance	(pair/ground)	≤ 1500 pF/km
Characteristic impedance	(1-100 MHz)	(100 ± 5) Ω
Nominal velocity of propagation		ca. 79 %
Propagation delay		≤ 427 ns/100m
Delay skew		≤ 12 ns/100m
Test voltage	(DC, 1 min) core/core and core/screen	1000 V
Transfer impedance	at 1 MHz	10 mΩ/m
	at 10 MHz	10 mΩ/m
	at 30 MHz	30 mΩ/m
	at 100MHz	60 mΩ/m
Coupling attenuation		85 dB

Electrical data (nominal)

acc. to Cat.7 (at 20°C)

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)	Return loss (dB)
1.0	1.8	100	97	98	95	105	105	-
4.0	3.4	100	97	97	94	105	102	27
10.0	5.4	100	97	95	92	97	94	30
16.0	6.8	100	97	93	90	93	90	30
20.0	7.7	100	97	92	89	91	88	30
31.2	9.6	100	97	90	87	87	84	30
62.5	13.7	100	97	86	83	81	78	30
100.0	17.4	100	97	83	80	77	74	30
125.0	19.5	95	92	75	72	75	72	26
155.5	21.9	94	91	72	69	73	70	26
175.0	23.3	93	90	70	67	72	69	25
200.0	25.0	92	89	67	64	71	68	25
250.0	28.1	90	87	62	59	69	66	24
300.0	30.9	89	86	58	55	67	64	24
450.0	38.3	87	84	48	45	64	61	23
600.0	44.8	85	82	40	37	61	58	22
750.0	52.0	83	80	31	28	59	56	21
900.0	59.4	82	79	23	20	58	55	20
1000,0	63,1	80	77	17	14	57	54	20

UC900 SS23 Cat.7 (L)H

Technical data

Product code	Cable type	Brand name	Outer diameter	Fire load		Weight	Copper content	Tensile force
				MJ/km	kWh/m			
			mm			kg/km		N
1001113	J/A-02YSC(L)H 4x2x056 PiMF	UC900 SS 23 Cat.7 S/FTP 4P (L)H LSHF	9.5	878	0.244	98	38	350
1020561	J/A-02YSC(L)H 4x2x056 PiMF LSHF- FR	UC900 SS 23 Cat.7 S/FTP 4P(L)H LSHF-FR	9.5	878	0.244	114	38	350

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2009, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.