


High Flex SMPTE 311M-HD-Hybrid-Camera Cable

Hybrid-HDTV-Camera Cable



Application

This Hybrid HD Camera Cable 2SM 9/125 + 4 x AWG20 + 2 x AWG24 acc. to SMPTE 311M-Standard contains Single-Mode Optical Fibres, Auxiliary- and Signal Conductors. It is used in professional video productions for simultaneous transmission of energy, video, audio and control signals and is intended to interconnect Camera Units and Base Stations in conjunction with the Connector Interface Standard. It is suitable for all new digital camera systems of well-known manufacturers.

Standards

SMPTE 311M

Flame resistance

FRNC jacket: IEC 60332-1, IEC 60754-2, IEC 61034

Construction

Element 1: Auxiliary Conductors AWG20 (4 x 0.6 mm²)

Conductor	tinned stranded copper wires, 19 x 0.20 mm, diameter 1.0 mm
Insulation	HDPE, diameter 1.5 mm
Identification	2 x black, 2 x white

Element 2: Signal Conductors AWG24 (2 x 0.22 mm²)

Conductor	tinned stranded copper wires, 7 x 0.20 mm, diameter 0.6 mm
Insulation	HDPE, diameter 1.1 mm
Identification	1 x red, 1 x grey

Element 3: Fibre Optic Single Mode (2 x 9/125µ)

Mode field diameter	at 1310 nm, diameter 9.5 µm ± 1 µm
Cladding diameter	diameter 125 µm ± 1 µm
Concentricity error	≤ 1 µm
Coating material	UV-cross-linked Acrylate, diameter 245 µm
Buffer material	Thermoplastic, diameter 0.9 µm ± 0.05 µm
Identification	1 x blue, 1x yellow

Element 4: Strength Member AWG16 (1 x 1.22 mm²)

Conductor	galvanized steel wires, diameter 1.6 mm
Insulation	HDPE, diameter 2.1 mm
Identification	1 x white

Cable lay up

Stranding	Core: 1 x Element 4, diameter 2.1 mm Layer: 4 x Element 1 + 2 x Element 2 + 2 x Element 3 and in the outer interstices 4 x fibrillated Polypropylene as needed for roundness, diameter 5.2 mm Sequence according to the above drawing
Wrapping	1 x non-woven fabric tape, diameter 5.4 mm

High Flex SMPTE 311M-HD-Hybrid-Camera Cable

Screen	Copper wire braid, tinned 95% opt. coverage, diameter 5.9 mm
Sheath	DMC FLEX PUR diameter 9.2 mm black, RAL 9005
Printing	DRAKA SMPTE 311 M Zero-Loss HD Cable Flex + batch number + meter marking

Mechanical properties

Temperature range PUR (FRNC)	during operation	- 40° C to + 70° C (-25°C to +70°C)
Max. humidity		95 %

Electrical properties

at 20°C

Auxiliary Conductors AWG20 (4 x 0.6 mm²)

DC resistance		≤ 35.3 Ω/km
Loop resistance		≤ 43 Ω/km
Insulation resistance		≥ 10 ⁴ MΩ*km
Test voltage		1750 V _{AC rms}
Operating voltage		≤ 300 V _{AC rms}

Signal Conductors AWG24 (2 x 0.22 mm²)

DC resistance		≤ 97.5 Ω/km
Loop resistance		≤ 184 Ω/km
Insulation resistance		≥ 10 ⁴ MΩ*km
Test voltage		1750 V _{AC rms}
Operating voltage		≤ 300 V _{AC rms}

Overall screen

DC resistance		≤ 20 Ω/km
---------------	--	-----------

Optical properties

at 20°C

Fibre Optic Single Mode (2 x 9/125μ)

Cut-off wavelength		1100 – 1350 nm
Attenuation	at 1310 nm	0.5 dB
Dispersion	at 1310 nm	3.5 ps/nm*km

Technical data

Product code	Type	Weight kg/km	Standard delivery length m	Drum size KTG	Copper content	Tensile force N	Minimum bending radius mm	Storage
1017104	SMPTE 311M Hybrid Camera Cable Flex	115	1000	081	47.2	800	65	inside