


## UC<sup>FUTURE</sup> COMPACT<sup>ZD</sup>26 Cat.7 S/FTP 24P LSHF-FR D<sub>ca</sub>

### S/FTP Data Centre Cable Cat. 7 AWG26/1



## Application

IEEE 802.3: 10Base-T; 100Base-T; 10GBase-T, ISDN; xDSL

IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s

PoE, PoE+

The conductor diameter is smaller compared to the standard installation cables. This leads to an increased attenuation and therefore the operating distance is reduced (60 m instead of 90 m installation cable in standard permanent link).

## Standards

IEC 61156-6 work area cable

ISO/IEC 11801

EN 50173-5; EN 50288-4-2

IEEE 802.3af

## Flame resistance

EN 50399: Class D<sub>cas</sub>2d1a1

LSHF-FR (LSOH-FR): IEC 60332-1; IEC 60332-3-24; IEC 60754-2; IEC 61034;

## Construction

Conductor	Bare copper wire, diameter 0.4 mm (AWG26/1)
Insulation	Foam-skin PP, diameter 1.0 mm
Twisting	2 insulated wires to the pair
Pair screening	Pet-Al foil around each pair
Stranding	6 (5+1) bundles with 4 foiled pairs bl, or, gn, br
	Coloured tapes are around each bundle
Screen	Tinned copper braid 85% coverage
Sheath	LSHF-FR D <sub>ca</sub> , diameter 13.9 mm
Printing	DRAKA UC <sup>Future</sup> COMPACT <sup>ZD</sup> 26 Cat.7 S/FTP 24P + batch number + meter marking

## Mechanical properties

Minimum bending radius	Without load	≥ 55 mm
	With load	≥ 110 mm
Temperature range	During operation	-20°C up to +60°C*
	During installation	10°C up to +40°C

**UC<sup>FUTURE</sup> COMPACT<sup>ZD</sup>26 Cat.7 S/FTP 24P LSHF-FR D<sub>ca</sub>**
**Electrical properties**
**at 20°C**

Loop resistance		≤ 280 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V <sub>bc</sub> 1 min
	core/screen	1000 V <sub>bc</sub> 1 min
Capacitance	800 Hz	nom. 44 nF/km
Capacitance unbalance		≤ 1600 pF/km
Mean characteristic impedance	100 MHz	100 Ω ± 5 Ω
Nominal velocity of propagation		ca. 76%
Insulation resistance	500 V	≥ 2000 MΩkm
Transfer impedance	bei 1 MHz	≤ 5 mΩ /m
	bei 10 MHz	≤ 5 mΩ /m
	bei 30 MHz	≤ 10 mΩ /m
Coupling attenuation		≥ 85 dB
Segregation classification acc. EN 50174-2		„D”

**Electrical Data (nominal)**
**acc. to Cat.7 (at 20°C)**

f (MHZ)	Attenuation (dB/10m)	NEXT (dB)	PS-NEXT (dB)	ACRF (dB/100m)	PS-ACRF (dB/100m)	Return loss (dB)
1,0	0,3	90	87	80	77	23
4,0	0,6	90	87	80	77	24
10,0	1,0	90	87	80	77	25
16,0	1,3	90	87	76	73	25
20,0	1,4	90	87	74	71	25
31,2	1,8	90	87	70	67	25
62,5	2,6	90	87	64	61	23
100,0	3,2	87	84	60	57	21
125,0	3,6	85	82	58	55	20
155,5	4,0	84	81	56	53	19
175,0	4,3	83	80	55	52	19
200,0	4,6	82	79	54	51	18
250,0	5,1	81	78	52	49	18
300,0	5,6	80	77	50	47	17
450,0	6,9	77	74	47	44	17
600,0	7,9	75	72	44	41	17

## UC<sup>FUTURE</sup> COMPACT<sup>ZD</sup>26 Cat.7 S/FTP 24P LSHF-FR D<sub>ca</sub>

### Product order data

Product Reference Code	Designation	Type	Outer diameter mm	Euro Class	Fire load		Weight kg/km	Copper content kg/km	Tensile force N
					MJ/km	kWh/km			
60013688	J-09YS(St)CH	UC <sup>FUTURE</sup> COMPACT <sup>ZD</sup> 26 Cat.7 S/FTP 24P LSHF-FR	13.9	D <sub>ca</sub> s2d1a1	2.171	0,603	205	90	500

### Product Code Table

Product Description	PG Reference Code	PG Part Number
UC <sup>FUTURE</sup> COMPACT <sup>ZD</sup> 26 Cat.7 S/FTP 24P LSHF-FR	60013688	60013688

\* POE, reduce temperature range

© PRYSMIAN GROUP 2011, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.