


Guitar Cable DMC 1/6

1x(1x0.22 mm²)

Guitar Cable



Application

Audio cables are used in professional broadcasting systems for the transmission of analogue audio signals

Standards

Flame resistance

Construction

Conductor	stranded copper wires, bare, 7 x 0.20, diameter 0.60 mm	
Insulation	PE, diameter 1.50 mm ± 0.05 mm	
Semi conductive skin	semi conducting PE, diameter 1.90 mm	
Screen	spiraled copper wires, bare, 56 x 0.10 mm, diameter 2.1 mm	
Sheath	DMC FLEX PVC, diameter 6.2 ± 0.3 mm matt black, RAL 9005	
Printing	DRAKA COMTEQ DMC 1/6	

Mechanical properties

Minimum bending radius	without load	≥ 25 x D (D= outer diameter)
	with load	≥ 50 x D (D= outer diameter)
Temperature range	during operation	- 30° C to + 70° C
	during installation	- 5° C to + 50° C

Electrical properties

at 20°C

DC resistance		≤ 90 Ω/km
Mutual capacitance	(1 kHz) conductor/screen	≤ 140 pF/m
Insulation resistance	500 V _{DC}	≥ 10 ⁴ MΩ*km
Test voltage	(50 Hz. 1 min) core/screen	1.0 kV _{rms}

Guitar Cable DMC 1/6

1x(1x0.22 mm²)

Technical data

Product code	Designation	Type	Brand name	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size *PWD	Gross weight kg	Copper content	Tensile force N
CT...	Li-2Y(hS)DY bk	1x2x0.22 ²	DMC 1/6	6.2	47	500	400/120/280	25.5	6.8	38
						100	Oneway drum	4.8		
CT...	gn	1x2x0.22 ²	DMC 1/6	6.2	47	500	400/120/280	25.5	6.8	38
						100	Oneway drum	4.8		
CT...	rd	1x2x0.22 ²	DMC 1/6	6.2	47	500	400/120/280	25.5	6.8	38
CT...	bl	1x2x0.22 ²	DMC 1/6	6.2	47	500	400/120/280	25.5	6.8	38

*PWD (plywood drum)

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2006, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.