

0.8L/3.7 Dz

High Flexible Video Cable 75 Ω



Application

Video cables are primary used in closed circuit TV systems and in studio applications.

Standards

For analogue and digital video signals (Composite, Component, SDI, SDV, SDTI, HDTV)

Flame resistance

Construction

Inner conductor	stranded copper wire, diameter 0.8 mm
Insulation	Foam-PE, diameter 3.7 mm
Outer conductor	2xCu-braid, tinned 4.6 mm
Sheath	DMC FLEX PVC diameter 5.9 mm black, RAL 9005
Printing	DRAKA COMTEQ - 0.8L/3.7Dz - 75 Ω ± 1% -HIGHFLEX HDTV 5GHz +metermarking

Electrical properties

at 20°C

DC resistance	Inner conductor	50 Ω/km
	Outer conductor	10 Ω/km
Mutual capacitance		56 pF/m
Characteristic impedance		75 Ω ± 0.75 Ω
Velocity ratio		78 %
Screening factor		> 90 dB

0.8L/3.7 Dz

Electrical data

at 20°C

Attenuation (dB/100m) nominal		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)	
1	1.0	50 – 300	> 26
10	2.9	300 – 3000	> 22
100	8.4	3000 – 3500	> 18
200	11.6	3500 – 5000	> 15
300	14.1		
500	18.6		
800	24.2		
1000	27		
1500	33.9		
2250	44.1		
3000	51.9		
3500	57.4		
4000	60.2		
4500	65.8		
5000	71.1		

Technical data

Product code	Type	Weight kg/km	Standard delivery length m	Drum size *PWD	Copper content	Tensile force N	Bending radius mm	Storage
1003605 CT2850500	0.8L/3.7Dz Flex PVC sw	49	1000	051	37.3	100	60	inside

*PWD (plywood drum)

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
DR 0.8L/3.7Dz PVC/rubber black HDTV		60014488	60014488
DR 0.8L/3.7Dz PVC/rubber HDTV 500DW	1003605-00500DW	60014488	60014489
DR 0.8L/3.7Dz PVC/rubber HDTV 1000DW	1003605-01000DW	60014488	60014492

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.