


UC400 Cat.6 U/UTP HD LSHF-FR

B2_{ca} s1a d1 a1

U/UTP Installation cable



Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T;
IEEE 802.5 16 MB; ISDN; TPDDI; ATM
Power over Ethernet (PoE) / Type 1-4

Standards

EIA/TIA-568-C.2
ISO/IEC 11801 2nd ed; IEC 61156-5;
EN 50173-1, EN 50288-6-1
IEEE 802.3af / at / bt

Flame resistance

EN 50399: Class B2_{ca}s1a1d1a1
LSHF-FR Cca (FRNC): IEC60332-3-24; IEC 60332-1; 60754-2; IEC 61034;

Construction

Conductor	Bare copper wire: Nom. 0,54
Insulation	Polyethylene, Ø 0.95 mm nom
Twisting	2 cores to the pair
Cable lay up	4 pairs to the core non-metallic cross separator (spline)
Overall FR Tape	Glass Tape (GT)
Sheath	LSHF-FR blue RAL 5012 (alt colour: violet RAL4001)

Mechanical properties

Minimum bending radius	Installation	8 x D
	Installed	4 x D
Temperature range	during operation	-20°C up to + 60°C
	during installation	0°C up to + 50°C

UC400 Cat.6 U/UTP HD LSHF-FR B2ca s1a d1 a1

Electrical properties

at 20°C

DC loop resistance	≤ 176 Ω /km
Resistance unbalance	≤ 2%
Insulation resistance (500 V)	≥ 5000 MΩ *km
Capacitance at 800 Hz	Nom. 48 nF/km
Capacitance unbalance (pair to ground)	≤ 1500 pF/km
Mean impedance 100 MHz	100 ± 5 Ω
Nominal velocity of propagation	Approx. 67 %
Propagation delay	Nominal 535 ns/100m
Delay skew	Nominal 20 ns/100m
Test voltage (DC, 1 min)	1000 V
Core/Core	

Electrical data (nominal)

acc. to Cat.6 (at 20°C)

f (MHz)	Attenuation (dB/100m)		NEXT (dB)		PS-NEXT (dB)		ACR (dB/100m)		PS-ACR (dB/100m)		ELFEXT (dB/100m)		PS-ELFEXT (dB/100m)		Return loss (dB)	
	max.	Nom.	min	nom.	min.	Nom.	Min.	Nom.	Min.	Nom.	min.	Nom.	min.	Nom.	min.	Nom.
1	2.1	1.9	74	78	72	75	72.0	76.1	70.0	73.1	68	82	65	80	20	22
4	3.8	3.8	65	69	63	66	61.2	65.2	59.2	62.2	56	70	53	68	23	25
10	6.0	6.0	59	63	57	60	53.0	57.0	51.0	54.0	48	62	45	60	25	27
16	7.6	7.6	56	60	54	57	48.4	52.3	46.4	49.3	44	58	41	56	25	27
20	8.5	8.5	55	59	53	56	46.5	50.0	44.5	47.0	42	56	39	54	25	27
31.2	10.7	10.7	52	56	50	53	41.3	45.0	39.3	42.0	38	52	35	50	23.6	26
62.5	15.5	15.1	47	51	45	48	31.5	36.0	29.5	33.0	32	46	29	44	21.5	24
100	19.9	19.1	44	48	42	45	24.1	28.9	22.1	25.9	28	42	25	40	20.1	23
125	22.5	21.3	43	47	41	44	20.5	25.2	18.5	22.2	26	40	23	38	19.5	22
155.5	25.4	23.8	42	45	40	42	16.6	21.3	14.6	18.3	24	38	21	36	18.8	21
175	27.1	25.3	41	44	39	41	13.9	19.1	11.9	16.1	23	37	20	35	18.4	21
200	29.2	27.0	40	44	38	41	10.8	16.5	8.8	13.5	22	36	19	34	18.0	20
250	33.0	32.0	38	42	36	39	5.0	10.0	2.0	7.0	20	34	17	32	17.3	19
300		36.1		41		38		4.8		1.8		32		30		19
400		41.7		39		36		-2.7		-5.7		30		28		18

Technical data

Product Reference Code	Productname	Outer diameter mm	Euro Class	Fire load		Weight kg/km	Copper index	Tensile force N
				MJ/km	kWh/m			
60067034	UC400 C6 U/UTP GT LSHF-FR B2ca	7.1	B2ca s1a d1a1	747	0,22	38	18.1	100