


# UC500 S23 Cat.6<sub>A</sub> LSHF D<sub>ca</sub>

**U/FTP AWG23/1**



## Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T  
IEEE 802.5 16 MB; ISDN; FDDI; ATM  
Power over Ethernet (PoE) / Type 1-4

## Standards

ISO/IEC 11801, IEC 61156-5  
EN 50173-1, EN 50288-10  
IEEE 802.3af / at / bt

## Flame resistance

EN 50399: Class D<sub>ca</sub> s2d2a1  
LSHF D<sub>ca</sub>: IEC 60332-1; IEC 60754-2; IEC 61034

## Construction

Conductor	bare copper wire, Ø 0.56 mm (AWG23/1)
Insulation	Foamskin Polyethylene, Ø 1.35 mm
Twisting	2 cores to the pair
Pair screen	<b>High Performance STP:</b> Al-laminated plastic foil, patented wrapping of two pairs each, drain wire AWG26 tinned
Cable lay up	2x2 pairs to the core
Sheath	LSHF D <sub>ca</sub> , blue RAL 5024

## Mechanical properties

Bending radius	Installation	8 x Outer diameter
	Installed	4 x Outer diameter
Temperature range	During operation	-20°C to + 60°C
	During installation	0°C to + 50°C

## UC500 S23 Cat.6<sub>A</sub> LSHF D<sub>ca</sub>

### Electrical properties

at 20°C ± 5°C

Loop resistance		154 Ω/km	
Resistance unbalance		≤ 2%	
Insulation resistance	(500 V)	≥ 2000 MΩ *km	
Mutual capacitance	at 800 Hz	Nom. 43 nF/km	
Capacitance unbalance	(pair/ground)	≤ 1500 pF/km	
Mean characteristic impedance	100 MHz	100 ± 5Ω	
Nominal velocity of propagation		Ca. 79 %	
Propagation delay	Nominal	≤ 427 ns/100m	
Delay skew	Nominal	≤ 12 ns/100m	
Test voltage	(DC, 1 min) core/ core and core/screen	1000 V	
Transfer impedance	at 1 MHz	≤ 50 mΩ /m	Grade 2
	at 10 MHz	≤ 100 mΩ /m	
	at 30 MHz	≤ 200 mΩ /m	
Coupling attenuation		55 dB	Type 2
Segregation classification acc. EN 50174-2		"c"	

### Electrical data (nominal)

acc. to Cat.6<sub>A</sub> (at 20°C)

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ACRF (dB/100m)	PS-ACRF (dB/100m)	Return loss (dB)
1.0	1.8	100	97	98	95	105	105	-
4.0	3.4	100	97	97	94	105	102	27
10.0	5.4	100	97	95	92	97	94	30
16.0	6.8	100	97	93	90	93	90	30
20.0	7.7	100	97	92	89	91	88	30
31.2	9.6	100	97	90	87	87	84	30
62.5	13.7	100	97	86	83	81	78	30
100.0	17.4	100	97	83	80	77	74	30
125.0	19.5	95	92	75	72	75	72	26
155.5	21.9	94	91	72	69	73	70	26
175.0	23.3	93	90	70	67	72	69	25
200.0	25.0	92	89	67	64	71	68	25
250.0	28.1	90	87	62	59	69	66	24
300.0	30.9	89	86	58	55	67	64	24
400.0	38.3	87	84	48	45	64	61	23
500.0	44.8	85	82	40	37	61	58	22

## UC500 S23 Cat.6<sub>A</sub> LSHF D<sub>ca</sub>

### Product order data

Product code	Cable type	Brand name	Outer diameter mm	CPR Euro Class	Fire load		Weight kg/km	Copper content	Tensile force
					MJ/km	kWh/m			N
60015537	J-02YS(St)H 4x2x0.56	UC500 S23 Cat.6 <sub>A</sub> 4P LSHF D <sub>ca</sub>	6.9	D <sub>ca</sub> s2d2a1	493	0.137	45	24	100
60015554	J-02YS(St)H 2x4x2x0.56	UC500 S23 Cat.6 <sub>A</sub> 2x4P LSHF D <sub>ca</sub>	6.9 x 13.9	D <sub>ca</sub> s2d2a1	986	0.274	90	48	200

### Product Code Table

Product Description	PG Reference Code	PG Part Number
UC500 S23 C6A U/FTP 4P LSHF D <sub>ca</sub>	60015537	<b>60015537</b>
UC500 S23 C6A U/FTP 4P LSHF D <sub>ca</sub> 305BR	60015537	<b>60011113</b>
UC500 S23 C6A U/FTP 4P LSHF D <sub>ca</sub> 500DW	60015537	<b>60011412</b>
UC500 S23 C6A U/FTP 4P LSHF D <sub>ca</sub> 1000DW	60015537	<b>60011413</b>
UC500 S23 C6A U/FTP 2x4P LSHF D <sub>ca</sub>	60015554	<b>60015554</b>
UC500 S23 C6A U/FTP 2x4P LSHF D <sub>ca</sub> 500DW	60015554	<b>60015555</b>
UC500 S23 C6A U/FTP 2x4P LSHF D <sub>ca</sub> 500DP	60015554	<b>60015557</b>

© PRYSMIAN GROUP 2011, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.