


## UC500 23 U/UTP Cat.6<sub>A</sub> Z1s LSHF



### Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T ; 10000Base-T (10G)  
IEEE 802.5 16 MB; ISDN; FDDI; ATM  
Power over Ethernet (PoE) / Type 1-4

### Standards

EIA/TIA 568-C.2  
ISO/IEC 11801 2<sup>nd</sup> ed; IEC 61156-5  
EN 50173; EN 50288-11-1  
IEEE 802.3af / at / bt

### Fire rating

EN50399: Class E<sub>c</sub>  
LSHF (LSOH): IEC 60332-1; IEC 60754-2; IEC 61034; a

### Construction

Conductor	bare copper wire Ø 0.565 mm (AWG23)
Insulation	Solid Polyethylene, Ø 1.18 mm nom
Twisting	2 cores to the pair
Cable lay up	1x4 pairs to the core
Overall screen	Patented 10G-Folie Zebra tape no-continuity
Sheath	7.70mm - LSHF RAL 5024

### Mechanical Properties

Bending radius	without load	4 x OD
	with load	8 x OD
Temperature range	during operation	-20°C to + 60°C
	during installation	0°C to + 50°C

## UC500 23 U/UTP Cat.6<sub>A</sub> Z1s LSHF

### Electrical Properties

at 20°C ± 5°C

DC loop resistance		≤ 158 Ω/km
Resistance unbalance		≤ 2%
Insulation resistance	(500 V)	≥ 2000 MΩxkm
Capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance	(pair to ground)	≤ 1500 pF/km
Nominal velocity of propagation		approx. 66%
Propagation delay		≤ 427 ns/100 m
Delay skew		≤ 12 ns/100 m
Test voltage	(DC, 1 min) Core/Core and Core/Screen	1000 V
Coupling attenuation		≥ 40 dB
Segregation classification acc. EN 50174-2		„C“

### Electrical data (nominal)

acc. to Cat.6<sub>A</sub> (at 20°C)

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)	Return loss (dB)
1.0	2.1	75.0	72.0	67.0	65.0	20.0
4.0	3.8	66.0	63.0	55.0	53.0	23.0
10.0	5.9	60.0	57.0	47.0	45.0	25.0
16.0	7.5	57.0	54.0	43.0	41.0	25.0
20.0	8.4	56.0	53.0	41.0	39.0	25.0
31.2	10.5	53.0	50.0	37.0	35.0	24.0
62.5	15.0	48.0	45.0	31.0	29.0	22.0
100.0	19.1	45.0	42.0	27.0	25.0	20.0
125.0	21.5	44.0	41.0	25.0	23.0	19.0
155.5	24.1	43.0	40.0	23.0	21.0	19.0
175.0	25.7	42.0	39.0	22.0	20.0	18.0
200.0	27.6	41.0	38.0	21.0	19.0	18.0
250.0	31.1	38.3	36.0	19.0	17.0	17.3
500.0	45.3	33.8	31.8	13.8	11.8	17.3

### Product order data

Product code	Brand name	Euro class	Outer diameter mm	Fire load		Weight kg/km	Copper content	Tensile force
				MJ/km	kWh/m			N
60027810	UC500 23 U/UTP Cat.6 <sub>A</sub> Z1s LSHF	E <sub>ca</sub>	7.7	585	0,163	54	24	100

© PRYSMIAN GROUP 2013, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.