


UC^{FUTURE} COMPACT^{ZD}26 Cat.7 S/FTP LSHF Indoor / Outdoor FireBur® sheath, AWG26/1



Eca
CPR

Application

IEEE 802.3: 10Base-T; 100Base-T; 10GBase-T, ISDN; xDSL
IEEE 802.5 16 MB; ISDN; TPDDI; ATM155Mbit/s
Power over Ethernet (PoE) / PoE+
IP cameras

The conductor diameter is smaller compared to the standard installation cables. This leads to an increased attenuation and therefore the operating distance is reduced (60 m instead of 90 m installation cable in standard permanent link).

Standards

IEC 61156-6 work area cable; EN 50288-4-2
ISO/IEC 11801;. EN 50173-5
IEEE 802.3af

Flame resistance

EN50399: Euro Class E_{ca}
LSHF (LSOH): IEC 60332-1; IEC 60754-2; IEC 61034;

Construction

Conductor	Bare copper wire, diameter 0.4 mm (AWG26/1)
Insulation	Foam skin PP, diameter 1.0 mm (+/- 0,05)
Twisting	2 cores to the pair
Pair screening	Pet-Al foil around each pair
Screen	Tinned copper braid approx. 60% coverage
Sheath	1.0 mm black FireBur® sheath, UV stabilised, IEC 50290-2-27
Printing	DRAKA UC ^{Future} COMPACT ^{ZD} 26 Cat.7 S/FTP Indoor-Outdoor + batch number + meter marking

Mechanical properties

Minimum bending radius	Without load	8xD
	With load	4xD
Temperature range	During operation	-20°C up to +60°C*
	During installation	10°C up to +40°C

* POE, reduce temperature range

UC^{FUTURE} COMPACT^{ZD}26 Cat.7 S/FTP LSHF Indoor / Outdoor

Electrical properties

at 20°C

Loop resistance		≤ 280 Ω/km
Resistance unbalance		≤ 2%
Test voltage	core/core	1000 V _{bc} 1 min
	core/screen	1000 V _{bc} 1 min
Capacitance	800 Hz	nom. 44 nF/km
Capacitance unbalance		≤ 1600 pF/km
Mean characteristic impedance	100 MHz	100 Ω ± 5 Ω
Nominal velocity of propagation		ca. 76%
Insulation resistance	500 V	≥ 2000 MΩkm
Coupling attenuation		≥ 85 dB

Electrical Data (nominal)

acc. to Cat.7 (at 20°C)

f (MHZ)	Attenuation (dB/10m)	NEXT (dB)	PS-NEXT (dB)	ACRF (dB/100m)	PS-ACRF (dB/100m)	Return loss (dB)
1,0	0,3	90	87	80	77	23
4,0	0,6	90	87	80	77	24
10,0	1,0	90	87	80	77	25
16,0	1,3	90	87	76	73	25
20,0	1,4	90	87	74	71	25
31,2	1,8	90	87	70	67	25
62,5	2,6	90	87	64	61	23
100,0	3,2	87	84	60	57	21
125,0	3,6	85	82	58	55	20
155,5	4,0	84	81	56	53	19
175,0	4,3	83	80	55	52	19
200,0	4,6	82	79	54	51	18
250,0	5,1	81	78	52	49	18
300,0	5,6	80	77	50	47	17
450,0	6,9	77	74	47	44	17
600,0	7,9	75	72	44	41	17

UC^{FUTURE} COMPACT^{ZD}26 Cat.7 S/FTP LSHF Indoor / Outdoor

Product order data

Product code	Designation	Type	Outer diameter mm	Euro class	Fire load		Weight kg/km	Copper content kg/km	Tensile force N
					MJ/km	kWh/m			
60042449	J-09YS(St)CH	4x2x0,4 PiMF	6.3	E _{ca}	282	0,08	41	21	100